

# Insulating Rubber Gloves

Manufactured using natural rubber in ISO manufacturing facilities the rubber insulating gloves provided by Cementex Products Inc. are compliant with OSHA 1910.137, OSHA 1910.268, NFPA 70E, CSA Z462, and exceed the ASTM D120 and European EN60903 standards for use around Electrical Hazards and Arc Flash Protection.

These gloves are made of natural rubber construction offering the required dielectric properties combined with flexibility, strength, and durability. Gloves feature rolled cuffs and are anatomically shaped thereby reducing hand fatigue. Each glove is chlorinated for maximum comfort. Gloves are available in whole sizes in Black, Red, or Yellow.

## Class / Voltage Usage

Each glove has colored label denoting class and maximum voltage the glove may be used for:

- Beige	Class 00	Max. Use Voltage	500VAC	/	750VDC
- Red	Class 0	Max. Use Voltage	1,000VAC	/	1,500VDC
- White	Class 1	Max. Use Voltage	7,500VAC	/	11,250VDC
- Yellow	Class 2	Max. Use Voltage	17,000VAC	/	25,500VDC
- Green	Class 3	Max. Use Voltage	26,500VAC	/	39,750VDC
- Orange	Class 4	Max. Use Voltage	36,000VAC	/	54,000VDC



**Sizing:** Measure the circumference of the palm as shown. Round up to the nearest whole number = Size

## Insulating Gloves

<b>PN</b> _____	<b>DESC</b> _____
IG00-11-(SIZE).....	Class 00 - 11" O.A.L.
IG00-14-(SIZE).....	Class 00 - 14" O.A.L.
IG0-11-(SIZE).....	Class 0 - 11" O.A.L.
IG0-14-(SIZE).....	Class 0 - 14" O.A.L.
IG1-14-(SIZE).....	Class 1 - 14" O.A.L.
IG1-16-(SIZE).....	Class 1 - 16" O.A.L.
IG2-14-(SIZE).....	Class 2 - 14" O.A.L.
IG2-16-(SIZE).....	Class 2 - 16" O.A.L.
IG2-18-(SIZE).....	Class 2 - 18" O.A.L.
IG3-16-(SIZE).....	Class 3 - 16" O.A.L.
IG4-16-(SIZE).....	Class 4 - 16" O.A.L.

## OSHA Certification Requirements

All Cementex gloves ship tested and certified according to OSHA regulation 1910.137(b)(2)(xii) which states the employer shall certify that equipment has been tested in accordance with the requirements of paragraph (b)(2)(viii), (b)(2)(ix), and (b)(2)(xi) of this section. The certification shall identify the equipment that passed the test and the date it was tested.

**Glove Color** - color may be specified by the addition of: (B = Black), (R = Red), (Y = Yellow) after the (SIZE) in the part number

## Glove Kits

Include Insulating Rubber Gloves, Protectors, and Canvas Storage Bag

<b>PN</b> _____	<b>DESC</b> _____
IGK00-11-(SIZE)....	Class 00 - 11" O.A.L.
IGK00-14-(SIZE)...	Class 00 - 14" O.A.L.
IGK0-11-(SIZE).....	Class 0 - 11" O.A.L.
IGK0-14-(SIZE).....	Class 0 - 14" O.A.L.
IGK1-14-(SIZE).....	Class 1 - 14" O.A.L.
IGK2-14-(SIZE).....	Class 2 - 14" O.A.L.
IGK2-16-(SIZE).....	Class 2 - 16" O.A.L.
IGK3-16-(SIZE).....	Class 3 - 16" O.A.L.
IGK4-16-(SIZE).....	Class 4 - 16" O.A.L.



Insulating Rubber Gloves