

3M Fire Protection Products
3M™ Fire Barrier Sealant IC 15WB+



Affordable & Lasting Solutions



The choice for contractors in need of a UL-listed product at a reasonable price.

3M™ Fire Barrier Sealant IC 15WB+ offers contractors an intumescent sealant that is UL-listed while helping to meet budget considerations. Designed for general purpose use, 3M™ Fire Barrier Sealant IC 15WB+ is UL-qualified and tested to ASTM E 814 for most common firestopping applications, including typical pipe and cable through-penetrations in walls and floors.

Plus, its yellow color allows it to be more easily identifiable to inspectors as being UL-tested when compared to the many red firestop materials on the market.



3M™ Fire Barrier Sealant IC 15WB+

Effective and easy to install, 3M™ Fire Barrier Sealant IC 15WB+ is part of a family of 3M fire protection products that offer affordable, long-lasting solutions in a variety of commercial and residential applications. And it's brought to you by 3M, the #1 brand preferred by firestop contractors.

- Versatile for use in multiple firestopping applications
- UL-listed systems for ratings up to 3 hours
- Cost-effective
- 250+ UL and Warnock Hersey Listings
- Easy to identify yellow color
- Easy to apply




3M™ Fire Barrier Sealant IC 15WB+ is a General Purpose Intumescent Sealant Ideal for Use on Walls, Floors and Ceilings

- HVAC Ducts and Vents
- Metal Pipe
- Plastic Pipe, including CPVC
- Blank Openings
- Cable Trays
- Insulated Pipe
- Pipe and Cable Through-Penetrations
- Busways
- Construction Joints
- Combos
- Concrete Floors

Easy to Identify

Inspectors can instantly recognize 3M™ Fire Barrier Sealant IC 15WB+ by its distinctive yellow color. Many firestop materials utilize red colors, which can make it harder to distinguish UL-qualified products from those that are not. The yellow color of 3M™ Fire Barrier Sealant IC 15WB+ allows it to be more easily identified as a high-quality, UL-tested product.



3M
Building and Commercial Services Division
 3M Center
 Building 223-2N-21
 St. Paul, MN 55144-1000
 800-328-1687
 www.3M.com/firestop



© 3M 2013. All rights reserved.
 Printed in U.S.A. 98-0213-4604-8

Important Notice to User:

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty and Limited Remedy: 3M warrants that each 3M Fire Protection Product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

Please recycle.

3M is a trademark of 3M. All other trademarks are the property of their respective owners.