



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG4700A LKG Dup RCPT, Ig, 15A 125V, L5-15R, or *Hubbell Wiring Devices*

Catalog Number	IG4700A
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Isolated Ground Industrial, Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, Nema L5-15R, Screw Terminal, Orange.
Weight per unit	0.0680 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Screw Terminals
Current Rating	15
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	4050
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	1,875
Wire Size	#18 to #10

Dimensions and Weight

Size	3.29 in x 1.70 in x 1.17 in
------	-----------------------------

Descriptions

Description	LKG DUP RCPT, IG, 15A 125V, L5-15R, OR
extra long description	HWDK IG4700A LKG DUP RCPT, IG, 15A
Features	<p>In February 1968, Hubbell patented the first isolated ground receptacle. Today - when a clean, noise-free ground is more important than ever—Hubbell is still setting the standard. Hubbell uses insulation barrier construction on many models to isolate the ground contacts from the mounting strap. The green grounding screw is connected directly to the grounding contacts. In this way, ground contacts are separated from the mounting strap and also from the conventional grounding system. The isolated ground circ</p>
Long Description	Locking Devices, Twist-Lock®, Isolated Ground Industrial, Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, NEMA L5-15R, Screw Terminal, Orange.
Product Type	LKG Dup RCPT, Ig, 15A 125V, L5-15R, or
Special Features	Isolated Ground



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585002392
Manufacturers Part Number	IG4700A
UPC	783585002392

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	Traditional Duplex

Packaging

Carton	1
Package	10
Weight Per each	0.068

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L6-15R
standard	Listed to UL 498