



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IR07 Dual Ir/Probe Thermometer

Klein Tools

| | |
|------------------|---|
| Catalog Number | IR07 |
| Manufacturer | Klein Tools |
| Description | The Klein Tools IR07 Is A Dual Ir (Infrared) Thermometer and Probe Thermometer. This Rugged Pocket Thermometer Measures Temperature From -40 to 572-Degrees Fahrenheit (-40 to 400-Degrees Celsius) For Both Ir and Probe Measurements. The Ir Thermometer Has A Distance-to-Spot Ratio Of 8:1 and The Target Laser Can Also Be Used As A Laser Pointer. The Probe Accurately Measures Air, Liquid and Surface Temps and Has A Convenient Hook For Hands Free Indoor Measurements. The IR07 Quickly Calculates Differential Tem |
| Weight per unit | 0.0870 (lbs/each) |
| Product Category | Meters, Panel Instruments |

Features

| | |
|----------------|---|
| Accuracy | -40 to 0° C: +/-2°; 1 to 300° C: +/- 1°C |
| display | Backlit LCD |
| included | IR07 Dual IR and Probe Thermometer; Pouch; Owner's Manual and 2 x AAA Batteries |
| Material | ABS, Polycarbonate |
| media | Yes |
| Overall Height | 0.95" (2.4 cm) |
| Overall Width | 1.67" (4.2 cm) |
| Range | -40° to 572° F (-40° to 300° C) |
| Response Time | IR <500 ms; Probe <20 s |

Dimensions and Weight

| | |
|----------------|-----------------|
| Overall Length | 5.82" (14.8 cm) |
|----------------|-----------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | DUAL IR/PROBE THERMOMETER |
| extra long description | KLEIN IR07 Dual IR/Probe Digital T |
| Features | The Klein Tools IR07 is a dual IR (infrared) thermometer and probe thermometer. This rugged pocket thermometer measures temperature from -40 to 572-Degrees Fahrenheit (-40 to 400-Degrees Celsius) for both IR and probe measurements. The IR thermometer has a Distance-to-Spot ratio of 8:1 and the target laser can also be used as a laser pointer. The Probe accurately measures air, liquid and surface temps and has a convenient hook for hands free indoor measurements. The IR07 quickly calculates differential tem |
| Long Description | The Klein Tools IR07 is a dual IR (infrared) thermometer and probe thermometer. This rugged pocket thermometer measures temperature from -40 to 572-Degrees Fahrenheit (-40 to 400-Degrees Celsius) for both IR and probe measurements. The IR thermometer has a Distance-to-Spot ratio of 8:1 and the target laser can also be used as a laser pointer. The Probe accurately measures air, liquid and surface temps and has a convenient hook for hands free indoor measurements. The IR07 quickly calculates differential tem |
| Product Type | Dual Ir/Probe Digital Thermometer |
| Special Features | Pocket Sized, IR and Probe Thermometer; Hanging Hook for Use with Air Vents |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Klein Tools |
| GTIN | 00092644691812 |
| Manufacturers Part Number | IR07 |
| UPC | 092644691812 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | TEST EQUIPMENT, TESTERS AND MULTIMETERS |
| Type | Pocket Infrared Thermometer with Laser and Temperature Probe |

Packaging

| | |
|-----------------|-------------------|
| Carton | 1 |
| Package | 4 |
| Weight | 3.60 oz (106.5 g) |
| Weight Per each | 0.087 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Temperature Measurement via IR (Infrared) and Probe |
| standard | IEC EN 61326-1:2013; EN61326-2-3:2013 |