

# Wire Stripper & Long-Nose Pliers

## *in One!*



## Now with Crimper

- Crimps non-insulated connectors, lugs and terminals.



MADE IN USA

**KLEIN TOOLS** 

For Professionals... Since 1857™

# All-Purpose Pliers

**JOURNEYMAN™**



**CUTS**

**STRIPS**

**LOOPS**

**SHEARS**

**Cuts, strips and loops**  
solid and stranded wire.

**Long nose** for grabbing and looping wire.

**Induction hardened** cutting knives for long life.

6-32 and 8-32 screw shearing.

**Hot-riveted joint** ensures smooth action and no handle wobble.

**Dual material** Journeyman™ handles provide better grip.

**Spring loaded** for self-opening action.



**NEW!**  
J207-8CR

J206-8C



Cat. No.	UPC 92644+	Features	Cuts and Strips	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness
J206-8C	38002-0	Spring action	8-16 AWG solid 10-18 AWG stranded	8.375" (212 mm)	2.25" (57 mm)	1" (25 mm)	.5" (13 mm)	.5" (13 mm)	.125" (3 mm)
J207-8CR	38405-9	Crimper	10-18 AWG solid 12-20 AWG stranded						

**NEW!**



**KLEIN TOOLS**  
EST. 1857  
For Professionals... Since 1857™

See our complete line of Journeyman™ Pliers at  
[www.kleintools.com](http://www.kleintools.com)



© 2015 Klein Tools, Inc.  
Lincolnshire, IL 60069  
96408 Rev. 07/15 A

# Wire Stripper & Long-Nose Pliers

## *in One!*



## Now with Crimper

- Crimps non-insulated connectors, lugs and terminals.



MADE IN USA

**KLEIN TOOLS** 

For Professionals... Since 1857™

# All-Purpose Pliers

**JOURNEYMAN™**



**CUTS**

**STRIPS**

**LOOPS**

**SHEARS**

**Cuts, strips and loops**  
solid and stranded wire.

**Long nose** for grabbing and looping wire.

**Induction hardened** cutting knives for long life.

6-32 and 8-32 screw shearing.

**Hot-riveted joint** ensures smooth action and no handle wobble.

**Dual material** Journeyman™ handles provide better grip.

**Spring loaded** for self-opening action.



**NEW!**  
J207-8CR

J206-8C



Cat. No.	UPC 92644+	Features	Cuts and Strips	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness
J206-8C	38002-0	Spring action	8-16 AWG solid 10-18 AWG stranded	8.375" (212 mm)	2.25" (57 mm)	1" (25 mm)	.5" (13 mm)	.5" (13 mm)	.125" (3 mm)
J207-8CR	38405-9	Crimper	10-18 AWG solid 12-20 AWG stranded						

**NEW!**



**KLEIN TOOLS**  
For Professionals... Since 1857™



See our complete line of Journeyman™ Pliers at  
[www.kleintools.com](http://www.kleintools.com)



© 2015 Klein Tools, Inc.  
Lincolnshire, IL 60069  
96408 Rev. 07/15 A