



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



JJS40 Tron Fast Acting Fuse Class T

Bussmann Fuses

| | |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | JJS40 |
| Manufacturer | Bussmann Fuses |
| Description | Eaton Bussmann Series JJS Fuse, Current-Limiting, Small Footprint, VFD Line Protection, 40 A, Class T, Non-Indicating, Ferrule End X Ferrule End, 200 Kaic At 600 V, Standard, 10, 600 V |
| Weight per unit | 0.5000 (lbs/each) |
| Product Category | Renewable & Non-Renewable |

Features

| | |
|------------------|-----------------------------------|
| amperage rating | 40 A |
| class | Class T |
| connection | Ferrule End X Ferrule End |
| dimensions | 1.5600 IN X 0.8100 IN X 0.8100 IN |
| interrupt rating | 200 kAIC at 600 Vac |
| media | Yes |

Dimensions and Weight

| | |
|------|-----------------------------------|
| Size | 1.00 In Diameter X 1.56 In Length |
|------|-----------------------------------|

Descriptions

| | |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | TRON FAST ACTING FUSE CLASS T |
| extra long description | BUSS JJS-40 TRON FAST ACTING FUSE C |
| Features | Bussmann's Class T current-limiting, fast-acting fuses. Provides 10X better current limitation to help prevent equipment damage caused by short-circuit events. 200 kA Interrupting rating complies with NEC Section 110.9 for today's large capacity systems. Small, space-saving fuses provide a high degree of current limitation on short-circuits for excellent component protection. |
| Long Description | Eaton Bussmann series JJS fuse, Current-limiting, Small footprint, VFD line protection, 40 A, Class T, Non-indicating, Ferrule end x ferrule end, 200 kAIC at 600 V, Standard, 10, 600 V |
| Product Type | Tron Fast Acting Fuse Class T |
| Special Features | Non-Indicating |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00051712628402 |
| Manufacturers Part Number | JJS-40 |
| UPC | 051712628402 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fuses & Fuse Accessories

Type FUSE

Packaging

Carton 1

Package 10

Weight Per each 0.5

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Facility: Safety and Security Systems

standard RoHS Compliant,CE Marked