

# Eaton KRP-C-1200SP

Catalog Number: KRP-C-1200SP

Eaton Bussmann Series Class L fuse, KRP-C, time-delay, current limiting fuse, 1200 A, interrupting rating of 300 kA at 600 Vac and 100 kA at 300 Vdc



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series KRP-C fuse	KRP-C-1200SP
<b>UPC</b>	<b>Product Length/Depth</b>
051712605120	10.75 in
<b>Product Height</b>	<b>Product Width</b>
2.78 in	2.78 in
<b>Product Weight</b>	<b>Warranty</b>
0.001 lb	Not Applicable
<b>Compliances</b>	
CE Marked	
RoHS Compliant	

## Electrical rating

### Amperage Rating

1200 A

### Interrupt rating

300 kAIC at 600 Vac

100 kAIC Vdc

### Response time

4 sec at 500%

### Voltage rating

600 Vac, 300 Vdc

## Physical details

### Packaging type

Standard

## General information

### Class

Class L

### Connection

Bolted blade end x bolted blade end

### Fuse indicator

Non-indicating

## Resources

### Catalogs

[Low Voltage Branch Circuit Fuse Chapter](#)

[Bussmann Full Line Catalog](#)

### Compliance information

[RoHS Search Tool](#)

### Multimedia

[Bussmann series Fuseology](#)

### Technical data sheets

[Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton KRP-C-1200SP

Catalog Number: KRP-C-1200SP

Eaton Bussmann Series Class L fuse, KRP-C, time-delay, current limiting fuse, 1200 A, interrupting rating of 300 kA at 600 Vac and 100 kA at 300 Vdc



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series KRP-C fuse	KRP-C-1200SP
<b>UPC</b>	<b>Product Length/Depth</b>
051712605120	10.75 in
<b>Product Height</b>	<b>Product Width</b>
2.78 in	2.78 in
<b>Product Weight</b>	<b>Warranty</b>
0.001 lb	Not Applicable
<b>Compliances</b>	
CE Marked	
RoHS Compliant	

## Electrical rating

### Amperage Rating

1200 A

### Interrupt rating

300 kAIC at 600 Vac

100 kAIC Vdc

### Response time

4 sec at 500%

### Voltage rating

600 Vac, 300 Vdc

## Physical details

### Packaging type

Standard

## General information

### Class

Class L

### Connection

Bolted blade end x bolted blade end

### Fuse indicator

Non-indicating

## Resources

### Catalogs

[Low Voltage Branch Circuit Fuse Chapter](#)

[Bussmann Full Line Catalog](#)

### Compliance information

[RoHS Search Tool](#)

### Multimedia

[Bussmann series Fuseology](#)

### Technical data sheets

[Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)