



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **KTEMRGLED121200K 12W Led Emergency Backup Kit W/1200LM Led Module** *Keystone Technologies*

Catalog Number	KTEMRGLED121200K
Manufacturer	Keystone Technologies
Description	Led Emergency Back-Up Kit, 12W Constant Wattage Driver & .70" X 8" Led Module, Approx 1200 Lumens. 90 Minute Operation, 120-277V Input, Remote Battery Pack. Includes Instruction Sheets, Test Switch, and Wiring Accessories. Individually Packaged
Weight per unit	2.5 (lbs/each)
Product Category	Lighting

### **Features**

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1200
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	12
Wire Type	N/A

### **Material, Color, and Finish**

Base Type	N/A
color rendering index (cri)	N/A
color temperature	N/A
housing color	N/A



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	N/A
Description	12W LED EMERGENCY BACKUP KIT W/1200LM LED MODULE
extra long description	Key KT-EMRG-LED-12-1200-K1-IP 28W,
Long Description	LED Emergency Back-Up Kit, 12W Constant Wattage Driver & .70" x 8" LED Module, Approx 1200 Lumens. 90 Minute Operation, 120-277V Input, Remote Battery Pack. Includes Instruction Sheets, Test Switch, and Wiring Accessories. Individually Packaged
Product Type	28W, 7" Round Ac Led Light Engine Kit, Phase Dimming, 90 Cri

## Manufacturer Information

Brand	Keystone
GTIN	00890949011652
Manufacturers Part Number	KT-EMRG-LED-12-1200-K1-IP
UPC	890949011652

## Taxonomies, Classifications, and Categories

Category Description	PHOTO & PROJECTION
----------------------	--------------------

## Packaging

Carton	1
Weight Per each	2.49

## Uses, Certifications, and Standards

Energy Star	Y
-------------	---