



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTLF32T8841HP 32W T8 48" 41K 3100LM 85CRI Med Bi-Pin Base

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | KTLF32T8841HP |
| Manufacturer | Keystone Technologies |
| Description | F32T8, 4100K, 85 Cri, High Performance Lamps, 25 PCS Per Carton |
| Weight per unit | 0.3800 (lbs/each) |
| Product Category | Linear Fluorescent Straight La |

Features

| | |
|-----------------|-------------------|
| Ballast Type | N/A |
| beam angle | 360 |
| Circuit Type | N/A |
| Input Voltage | Ballast Dependent |
| ip rating | N/A |
| lumens | 3100 |
| Nominal Length | 48 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 32 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|-------|
| Base Type | G13 |
| color rendering index (cri) | 80-89 |
| color temperature | 4100 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Glass |
| Description | 32W T8 48" 41K 3100LM 85CRI MED BI-PIN BASE |
| extra long description | Key KTL-F32T8-841-HP-DP Ignitor for |
| Long Description | F32T8, 4100K, 85 CRI, HIGH PERFORMANCE LAMPS, 25 PCS PER CARTON |
| Product Type | Ignitor For 750W Pulse Start MH |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Keystone |
| GTIN | 00890949006412 |
| Manufacturers Part Number | KTL-F32T8-841-HP-DP |
| UPC | 890949006412 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Packaging

Carton 25

Weight Per each 0.38

Uses, Certifications, and Standards

Energy Star N