

# Specifications

## Eaton LB17

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LB shape, 1/2"



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	LB17
<b>UPC</b>	782274512709
<b>PRODUCT LENGTH/DEPTH</b>	4.56 in
<b>PRODUCT HEIGHT</b>	2.25 in
<b>PRODUCT WIDTH</b>	1.38 in
<b>PRODUCT WEIGHT</b>	0.92 lb

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

## Product specifications

SHAPE	LB
TRADE SIZE	1/2"
MATERIAL	Feraloy iron alloy

## Resources

CATALOGS [Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS [Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)  
[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

INSTALLATION INSTRUCTIONS [IF 863 - Conduit Body Wire Pulling](#)  
[IF 964 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - LB17](#)  
[Condulet Form 7 Industrial Grade Conduit Bodies](#)

TECHNICAL SERVICE BULLETINS [Industrial Fittings Wire Fill Chart](#)  
[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications

## Eaton LB17

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LB shape, 1/2"



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	LB17
<b>UPC</b>	782274512709
<b>PRODUCT LENGTH/DEPTH</b>	4.56 in
<b>PRODUCT HEIGHT</b>	2.25 in
<b>PRODUCT WIDTH</b>	1.38 in
<b>PRODUCT WEIGHT</b>	0.92 lb

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

## Product specifications

SHAPE	LB
TRADE SIZE	1/2"
MATERIAL	Feraloy iron alloy

## Resources

CATALOGS [Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS [Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)  
[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

INSTALLATION INSTRUCTIONS [IF 863 - Conduit Body Wire Pulling](#)  
[IF 964 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - LB17](#)  
[Condulet Form 7 Industrial Grade Conduit Bodies](#)

TECHNICAL SERVICE BULLETINS [Industrial Fittings Wire Fill Chart](#)  
[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.