



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LBD2200 3/4" LBD MGL CNDT Body

Crouse-Hinds

Catalog Number	LBD2200
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet LBD Mogul Conduit Body, Feraloy Iron Alloy, 3/4"
Weight per unit	2.1 (lbs/each)
Product Category	Bodies & Covers

Features

connection	Threaded
dimensions	6.2500 IN X 1.5600 IN X 2.6300 IN

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Dimensions and Weight

Height	2-5/8
Hub Size	3/4 in
Length	6-1/4
Width	1-9/16

Descriptions

Description	3/4" LBD MGL CNDT BODY
extra long description	CRS-H LBD2200 3/4 IRON MOGUL OUTLET
Features	Crouse-Hinds series mogul bodies are installed in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of insulation. Mogul bodies provide longer openings needed when pulling large conductors and prevent sharp bends and kinks during installation. Mogul conduit bodies are manufactured in trade sizes 1/2" to 6" and are available in Feraloy iron alloy and copper-free aluminum. Our iron alloy bodies are available with a hot dip galvanized finish for added corrosion
Long Description	Eaton Crouse-Hinds series Condulet LBD mogul conduit body, Feraloy iron alloy, 3/4"
Product Type	3/4 Iron Mogul Outlet Body 90 Deg
Special Features	With Cover and Neoprene Gasket

Manufacturer Information

Brand	Crouse-Hinds
GTIN	00782274518206
Manufacturers Part Number	LBD2200
UPC	782274518206



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type Mogul conduit body

Packaging

Carton 5

Weight Per each 2.08

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Industrial Facilities/Factories - Other

standard UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D