



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LT112600 Non-UI 1-1/2" Seal Tight Metallic 600' Reel *Afc Cable*

Catalog Number	LT112600
Manufacturer	Afc Cable
Description	Non-UI Liquid-Tuff Liquidtight Conduit, Type VF, 6100 Series, Liquidtight Flexible Metal Conduit. Zinc Coated Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1-1/2 Inch Diameter, 600 Foot Reel
Weight per unit	540.0 (lbs/each)
Product Category	Flexible Metallic Conduit

### Features

Inside Diameter	1.380/1.410
Material	Steel
outside diameter	1.630/1.660

### Material, Color, and Finish

Color	Gray
Finish	PVC
Jacket Material	PVC

### Dimensions and Weight

Length	600
--------	-----

### Descriptions

Description	NON-UL 1-1/2" SEAL TIGHT METALLIC 600' REEL
extra long description	AFC 6106-62-00 1 1/2 LIQUID-TUFF VF
Features	LIQUID-TUFF™ Liquidtight, Flexible Steel Conduit, Type VF is a general purpose Non-UL raceway that is oil and sunlight resistant. Designed to be used for specific applications where Underwriters Laboratories Inc. (UL) or other agency approvals are not required.
Long Description	Non-UL LIQUID-TUFF Liquidtight Conduit, Type VF, 6100 Series, Liquidtight Flexible Metal Conduit. Zinc Coated Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1-1/2 inch Diameter, 600 Foot Reel
Product Type	1 1/2 Liquid-Tuff VF LT 600RL
Short Description	1 1/2 LIQUID-TUFF VF LT 600RL

### Manufacturer Information

Brand	AFC CABLE SYSTEMS
GTIN	00077680137838
Manufacturers Part Number	6106-62-00
UPC	077680137838



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Metal Conduit

## Trade Size

Trade Size	1-1/2
------------	-------

## Packaging

Carton	1
Package	600
Weight	0.98
Weight Per each	540

## Uses, Certifications, and Standards

Application	600 V and lower circuits.
Temperature Rating	140