



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

112 Pearl Street
67801-0000, KS Dodge City
Phone: 620-682-8503
Fax: 620-682-8504



LSF120SFTRPC 50/70/90/120W Led Flood 3K/4K/5K SLPFTR & Trun MNT

Cooper Lighting Solutions

Catalog Number	LSF120SFTRPC
Manufacturer	Cooper Lighting Solutions
Description	LSF Floodlight, Slipfitter and Trunnion, Selectable CCT: 3000K/4000K/5000K, Selectable Lumens: 9000-12, 000-15, 000-20, 000, 120W, 70 Cri, 120-347V, 50-60 HZ, Dusk-to-Dawn Via Button-Type Photocontrol
Weight per unit	12.5 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.34A at 347V
Fixture Type	FLOODLIGHT
Lamp Type	LED
lumens	20000
Voltage Rating	120-347V

Dimensions and Weight

Size	19.6 IN Length 12.0 IN Width 4.3 IN Height
------	--

Descriptions

Description	50/70/90/120W LED FLOOD 3K/4K/5K SLPFTR & TRUN MNT
extra long description	CLS LSF120-SFTR-PC CCT SELECT FLOOD
Long Description	LSF Floodlight, Slipfitter and Trunnion, Selectable CCT: 3000K/4000K/5000K, Selectable Lumens: 9000-12,000-15,000-20,000, 120W, 70 CRI, 120-347V, 50-60 Hz, Dusk-to-Dawn via Button-type photocontrol
Product Type	CCT Select Flood, 120W, SF & TRN, PC
Special Features	Available in selectable CCT and selectable lumens

Manufacturer Information

Brand	LUMARK INDOOR
GTIN	00080083305278
Manufacturers Part Number	LSF120-SFTR-PC
UPC	080083305278

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	12.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

112 Pearl Street
67801-0000, KS Dodge City
Phone: 620-682-8503
Fax: 620-682-8504

Uses, Certifications, and Standards

Application	lighting
Mounting	Slipfitter/Trunnion
standard	ISO Certified;DLC Qualified;1.5G Vibration Rated;FCC Class A;IP65 Rated;UL Listed;RoHS Compliant