



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DB Non-III Mom PB Sil-BZL FLSH Blu

Eaton Corp

Catalog Number	M22DB
Manufacturer	Eaton Corp
Description	Eaton 22.5 MM RMO-Titan Pushbutton, Blue Actuator, Silver Bezel, IP67, IP69K, Non-Illuminated, Flush Mounting, Nema 4X, 13, 5, 000, 000 Operations, Momentary, 22.5 MM, Flush Pushbutton, M22
Weight per unit	1.0 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

action	Blue
actuator	Flush, Button
operating cycles	5 million

Dimensions and Weight

Depth	2
Height	1
Size	22.5 mm
Width	2

Descriptions

Description	NON-ILL MOM PB SIL-BZL FLSH BLU
extra long description	ETN M22-D-B NON-ILL MOM PB SIL-BZL
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton 22.5 mm RMO-Titan Pushbutton,Blue Actuator,Silver bezel,IP67, IP69K,Non-Illuminated,Flush mounting,NEMA 4X, 13,5,000,000 operations,Momentary,22.5 mm,Flush Pushbutton,M22
Product Type	Non-III Mom PB Sil-BZL FLSH Blu

Manufacturer Information

Brand	Eaton
GTIN	00786685275970
Manufacturers Part Number	M22-D-B
Model	Modular pushbutton
UPC	786685275970



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description PUSHBUTTONS & CHIMES

Packaging

Carton 1

Weight Per each 1

Uses, Certifications, and Standards

Application Stationary Machinery and Equipment Outside Factory -
Stationary Machinery and Equipment Outside Factory - Other
environmental conditions IP67, IP69K, NEMA 4X, NEMA 13
Mounting FLUSH
standard CSA Certified,Lloyd's Register Certified,CCC Marked,Bureau
Veritas,GoST-R,CE Marked