



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22SDG Non-III Mom PB BLK-BZL FLSH GRN Eaton Corp

Catalog Number	M22SDG
Manufacturer	Eaton Corp
Description	Eaton 22.5 MM RMQ-Titan Pushbutton, Green Actuator, Black Bezel, IP67, IP69K, Non-Illuminated, Flush Mounting, Nema 4X, 13, 5, 000, 000 Operations, Momentary, 22.5 MM, Flush Pushbutton, M22
Weight per unit	0.0400 (lbs/each)
Product Category	Push Button Complete Assembleie

Features

action	Green
actuator	Flush, Button
operating cycles	5 million

Dimensions and Weight

Depth	2
Height	1
Size	22.5 mm
Width	2

Descriptions

Description	NON-ILL MOM PB BLK-BZL FLSH GRN
extra long description	ETN M22S-D-G NON-ILL MOM PB BLK-BZL
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton 22.5 mm RMQ-Titan Pushbutton, Green Actuator, Black bezel, IP67, IP69K, Non-illuminated, Flush mounting, NEMA 4X, 13,5,000,000 operations, Momentary, 22.5 mm, Flush Pushbutton, M22
Product Type	Non-III Mom PB BLK-BZL FLSH GRN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685275352
Manufacturers Part Number	M22S-D-G
Model	Modular pushbutton
UPC	786685275352

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
----------------------	-----------------------------

Packaging

Carton	1
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
Mounting standard	FLUSH Lloyd's Register Certified, CSA Certified, CCC Marked, CE Marked, Bureau Veritas, GoST-R