



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1  
78626-0000, TX Georgetown  
Phone: 737-444-2615  
Fax: 737-444-2617



## MACLLFQWH Maestro 1.5A/75W Fan/LT SP White

*Lutron*

Catalog Number	MACLLFQWH
Manufacturer	Lutron
Description	Maestro Led+ Fan/Light Control, Single-Pole, 120V/75W Dimmable Led or 250W Incandescent/Halogen Light, 1.5A Fan In White, Ed Box Packaging
Weight per unit	0.3000 (lbs/each)
Product Category	Fan Speed Switches & Controls

### Features

actuator	Tapswitch
amperage rating	1.5 A fan
connection	Screw Terminal
Contact Configuration	N-O
Contact Rating	1.5 A fan
media	Yes
Voltage Rating	120
Wattage	75 W dimmable LED/CFL or 250 W incandescent/halogen light

### Material, Color, and Finish

Color	White
Finish	Gloss

### Dimensions and Weight

Size	4.69 x 2.94
------	-------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1  
78626-0000, TX Georgetown  
Phone: 737-444-2615  
Fax: 737-444-2617

## Descriptions

Description	MAESTRO 1.5A/75W FAN/LT SP WHITE
extra long description	LUT MACL-LFQ-WH MACL FAN LIGHT WHIT
Features	The Lutron Maestro Dual LED+ Dimmer and 4-Speed Fan Control helps you achieve the ideal comfort level for your home. It includes the most advanced technology for superior dimming and adjust the fan speed all from one wall control. The top section is a LED+ Dimmer that works with up to 75W of dimmable LEDs or up to 250W of Incandescent/Halogen bulbs. The bottom section is a 4-speed fan control for a single ceiling paddle fan up to 1.5A. Press the tap switch once to toggle the light or fan ON to a programmed
Long Description	Maestro LED+ Fan/Light Control, Single-pole, 120V/75W Dimmable LED or 250W Incandescent/Halogen light, 1.5A fan in White, ED Box packaging
Product Type	MacL Fan Light White
Special Features	Dimmer (top) Tap on dimmer to preset light level; tap off. Tap twice for full on. Touch rocker to adjust light level. Fan control (bottom) Tap on to preset fan speed; tap off. Touch rocker to adjust speed. 4-quiet fan speeds plus off provide enhanced comfort. Designed to prevent motor hum. For use with only one fan/light.

## Manufacturer Information

Brand	Lutron
GTIN	00784276239523
Manufacturers Part Number	MACL-LFQ-WH
UPC	784276239523

## Taxonomies, Classifications, and Categories

Category Description	CEILING FANS AND ACCESSORIES
Type	Digital preset fan/light control

## Packaging

Carton	24
Package	48
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Lighting and Fan Control
Enclosure	Plastic
Mounting	WALLBOX