



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MAPROLA Maestro Pro Led Dimmer Light Almond Lutron

| | |
|------------------|--|
| Catalog Number | MAPROLA |
| Manufacturer | Lutron |
| Description | Maestro Pro Led+ Dimmer, Single-Pole, 3-Way, Multilocation, Light Almond |
| Weight per unit | 0.2700 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|-----------------|----------------|
| actuator | Tapswitch |
| connection | Screw Terminal |
| Connection Type | Screw Terminal |
| insulation | Plastic |
| Material | Plastic/Metal |
| media | Yes |
| Poles | 1 |
| Switch Type | Tapswitch |
| Voltage Rating | 120 |
| Wattage | 600 |

Material, Color, and Finish

| | |
|--------|--------------|
| Color | Light Almond |
| Finish | Gloss |

Dimensions and Weight

| | |
|------|----------------------|
| Size | 4.69 x 2.94;119 x 75 |
|------|----------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | MAESTRO PRO LED DIMMER LIGHT ALMOND |
| extra long description | LUT MA-PRO-LA MAESTRO PRO LED DIMME |
| Features | The Maestro PRO LED+ Neutral Optional Dimmer Switch features advanced phase selectable dimming, color change kits, and is designed for a broader compatibility range of high efficiency lighting. UL listed to control dimmable LEDs with integrated drivers, ELV, MLV, incandescent, and halogen loads as well as Phillips Mark 10® ballasts and Lutron Hi-Lume 1% 2-Wire (LTE) LED drivers. The large decorator style tap switch turns lights on/off and the dimming buttons allows for local fine-tune dimming. Works with u |
| Long Description | Maestro PRO LED+ Dimmer, Single-pole, 3-way, multilocation, Light Almond |
| Product Type | Maestro Pro Led Dimmer La |
| Special Features | Controls dimmable 150 W LED/CFL (screw-base) or 600 W incandescent/halogen loads. Provides true dimming from each location (with companion dimmers). Provides reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Lutron |
| GTIN | 00784276261623 |
| Manufacturers Part Number | MA-PRO-LA |
| UPC | 784276261623 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Digital fade dimmer, multi-location/3-way/single-pole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.27 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Lighting Control |
| Enclosure | Plastic |
| environmental conditions | 0 to 90% humidity, non-condensing. Indoor use only. |
| Frequency Rating | 50 to 60 |
| Mounting | WALLBOX |
| Operating Temperature | 32 to 104 |
| standard | UL, CSA, NOM |