



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

MC1222WG1000 12/2/2 WG MC (BK-RD)(WH-BK)(WH-RD) 1000'

Southwire Company

| | |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | MC1222WG1000 |
| Manufacturer | Southwire Company |
| Description | Southwire Armorlite Type MC Cable Is Constructed With Soft-Drawn Copper Type THHN/THWN-2 Conductors Rated 90°C Dry and A Bare Copper Grounding Conductor For Sizes 1/0 Awg and Larger. The Conductors Are Cabled Together and A Binder Tape Bearing The Print Legend Is Wrapped Around The Assembly. Aluminum Interlocking Armor Is Applied Over The Assembly. Also Available In Steel. Conductors Are Black With Phase Identification. Colors Available Upon Request With Economic Order Quantity. |
| Weight per unit | 0.3900 (lbs/each) |
| Product Category | Conduit & Raceways |

Features

| | |
|----------------------|---------|
| Conductor Size | 12 |
| media | Yes |
| Number of Conductors | 2 |
| outside diameter | 0.53876 |
| Voltage Rating | 600V |

Material, Color, and Finish

| | |
|--------------------|----|
| Conductor Material | CU |
|--------------------|----|

Dimensions and Weight

| | |
|--------|------|
| Length | 1000 |
|--------|------|

Descriptions

| | |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | 12/2/2 WG MC (BK-RD)(WH-BK)(WH-RD) 1000' |
| extra long description | SWC 55499103 MCNP12/2SolBkRd 2#12N |
| Long Description | Southwire Armorlite Type MC Cable is constructed with soft-drawn copper Type THHN/THWN-2 conductors rated 90°C dry and a bare copper grounding conductor for sizes 1/0 AWG and larger. The conductors are cabled together and a binder tape bearing the print legend is wrapped around the assembly. Aluminum interlocking armor is applied over the assembly. Also available in steel. Conductors are black with phase identification. Colors available upon request with economic order quantity. |
| Product Type | MCNP12/2SOLBKRD 2#12N 12G AA 1000R |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Flexible Conduit |
| GTIN | 00032886071188 |
| Manufacturers Part Number | 55499103 |
| UPC | 032886071188 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------|
| Category Description | BX & MC |
| Type | NPP |

Packaging

| | |
|-----------------|---------|
| Carton | 1000 |
| Weight | 154.533 |
| Weight Per each | 0.39 |