




## NON-METALLIC LOW PROFILE WIU COVERS

Single Gang Flat Expandable While-In-Use Covers - Extra Duty®  
Horizontal/Vertical 16-in-1

C07.1



Catalog #: ML500G

### APPLICATIONS

Low profile design that is expandable for weatherproof protection while an outlet is in use.

### PRODUCT FEATURES

- Revolutionary patented design expands from 1" to 3" for while-in-use needs
- 100% paintable surface
- Ultra rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Includes attached gasket and mounting hardware

### UL LISTED

File E116141

### NEMA

3R Rated

### NEC

2014 Compliant (article 406.9A & B) Extra Duty Rated

### US PATENTS

8,101,861; 8,319,334; 8,053,671

### GENERAL PRODUCT INFORMATION

Color: Gray

### CONFIGURATION

Gangs: 1

### PRODUCT MEASUREMENTS

Depth: 1 in. to 3 in.  
Wt. Ea. (Lbs.): 0.410

### PACKAGING


Package Type: Shrink  
 Std. Pkg.: 10  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 41.00  
 Ship Carton Length (in.): 13.13  
 Ship Carton Width (in.): 4.38  
 Ship Carton Height (in.): 6.63  
 Ctn Weight (Lbs.): 4.10  
 Pallet Qty: 1800.00  
 UPC Number: 050169917411  
 I2of5: 50050169917416



## NON-METALLIC LOW PROFILE WIU COVERS

Single Gang Flat Expandable While-In-Use Covers - Extra Duty®  
Horizontal/Vertical 16-in-1

C07.1



Catalog #: ML500G

### APPLICATIONS

Low profile design that is expandable for weatherproof protection while an outlet is in use.

### PRODUCT FEATURES

- Revolutionary patented design expands from 1" to 3" for while-in-use needs
- 100% paintable surface
- Ultra rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Includes attached gasket and mounting hardware

### UL LISTED

File E116141

### NEMA

3R Rated

### NEC

2014 Compliant (article 406.9A & B) Extra Duty Rated

### US PATENTS

8,101,861; 8,319,334; 8,053,671

### GENERAL PRODUCT INFORMATION

Color: Gray

### CONFIGURATION

Gangs: 1

### PRODUCT MEASUREMENTS

Depth: 1 in. to 3 in.  
Wt. Ea. (Lbs.): 0.410

### PACKAGING

Package Type: Shrink  
 Std. Pkg.: 10  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 41.00  
 Ship Carton Length (in.): 13.13  
 Ship Carton Width (in.): 4.38  
 Ship Carton Height (in.): 6.63  
 Ctn Weight (Lbs.): 4.10  
 Pallet Qty: 1800.00  
 UPC Number: 050169917411  
 I2of5: 50050169917416