



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

MLT4SCP316 Pan-Steel MLT4S Cable Tie, SS 316, Standard *Panduit Corporation*

Catalog Number	MLT4SCP316
Manufacturer	Panduit Corporation
Description	The MLT4S-CP316 Self Locking Cable Tie Speeds Up Installation With A Unique Self-Locking Head Design That Locks Into Place At Any Part Of The Tie Body. The Smooth Surfaces and Rounded Edges Assure Cable Protection and Worker Safety While Providing A Strong, Durable Method Of Cabling Bundle. The MLT4S-CP316 Cable Tie Can Be Used In A Wide Range Of Indoor, Outdoor, and Underground Applications. Color Stainless Steel.
Weight per unit	0.0089 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	200

Dimensions and Weight

Length	14.3
--------	------

Descriptions

Description	PAN-STEEL MLT4S CABLE TIE, SS 316, STANDARD
extra long description	PAN MLT4S-CP316 Pan-Steel® MLT4S-CP
Long Description	The MLT4S-CP316 self locking cable tie speeds up installation with a unique self-locking head design that locks into place at any part of the tie body. The smooth surfaces and rounded edges assure cable protection and worker safety while providing a strong, durable method of cabling bundle. The MLT4S-CP316 cable tie can be used in a wide range of indoor, outdoor, and underground applications. Color Stainless Steel.
Product Type	Pan-Steel® MLT4S-CP316 Cable Tie, SS 316, Standard, 4" Dia.,
Special Features	Harsh

Manufacturer Information

Brand	Panduit®
GTIN	00074983544011
Manufacturers Part Number	MLT4S-CP316
UPC	074983544011

Taxonomies, Classifications, and Categories

Type	Cable Tie
------	-----------

Availability

minimum qty	100
-------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Weight Per each	0.0089

Uses, Certifications, and Standards

Application	Harsh Environment
standard	UL E56854,CE,ABS,GL,SAE,BV,LR,DNV