




**SINGLE GANG WIU COVERS**

Single Gang - While In use Covers - Extra Duty®  
Horizontal/Vertical 16-in-1

C04.1



Catalog #: MM420C

**APPLICATIONS**

Designed for use whenever weatherproof protection is required while an outlet is in use.

**PRODUCT FEATURES**

- High-impact polycarbonate construction provides maximum durability
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Includes attached gasket and mounting hardware
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Lockable tab

**UL LISTED**

File E116141

**NEMA**

3R Rated

**NEC**

2014 Compliant (article 406.9A & B) Extra Duty Rated

**US PATENTS**

7,348,486; 7,282,645; 7,119,277; 6,960,221; 6,790,816; 6,642,453

**GENERAL PRODUCT INFORMATION**

Color: Clear

**CONFIGURATION**

Gangs: 1

**PRODUCT MEASUREMENTS**

Depth: 2-3/4 in.  
Wt. Ea. (Lbs.): 0.531

**PACKAGING**


Package Type: Shrink  
 Std. Pkg.: 8  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 53.10  
 Ship Carton Length (in.): 24.125  
 Ship Carton Width (in.): 4.688  
 Ship Carton Height (in.): 6.25  
 Ctn Weight (Lbs.): 4.25  
 Pallet Qty: 640.00  
 UPC Number: 050169917275  
 I2of5: 50050169917270



**SINGLE GANG WIU COVERS**

Single Gang - While In use Covers - Extra Duty®  
Horizontal/Vertical 16-in-1

C04.1



Catalog #: MM420C

**APPLICATIONS**

Designed for use whenever weatherproof protection is required while an outlet is in use.

**PRODUCT FEATURES**

- High-impact polycarbonate construction provides maximum durability
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Includes attached gasket and mounting hardware
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Lockable tab

**UL LISTED**

File E116141

**NEMA**

3R Rated

**NEC**

2014 Compliant (article 406.9A & B) Extra Duty Rated

**US PATENTS**

7,348,486; 7,282,645; 7,119,277; 6,960,221; 6,790,816; 6,642,453

**GENERAL PRODUCT INFORMATION**

Color: Clear

**CONFIGURATION**

Gangs: 1

**PRODUCT MEASUREMENTS**

Depth: 2-3/4 in.  
Wt. Ea. (Lbs.): 0.531

**PACKAGING**

Package Type: Shrink  
 Std. Pkg.: 8  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 53.10  
 Ship Carton Length (in.): 24.125  
 Ship Carton Width (in.): 4.688  
 Ship Carton Height (in.): 6.25  
 Ctn Weight (Lbs.): 4.25  
 Pallet Qty: 640.00  
 UPC Number: 050169917275  
 I2of5: 50050169917270