

# Eaton N228ZN

Catalog Number: N228ZN

Eaton B-Line series spring nut, 0.85"Hx1.875"Lx1.375"W, Steel, Electro-plated, 3/8"-16 bolt size, 1100 lbs load, 800 lbs load

## General specifications



|                                |                      |
|--------------------------------|----------------------|
| Product Name                   | Catalog Number       |
| Eaton B-Line series spring nut | N228ZN               |
| UPC                            | Product Length/Depth |
| 781011403638                   | 1.875 in             |
| Product Height                 | Product Width        |
| 0.85 in                        | 1.375 in             |
| Product Weight                 | Certifications       |
| 0.083 lb                       | Not Applicable       |

## Model

### Bolt/thread/rod size

3/8"-16

### Product Category

Channel nuts

### Type

Nut without spring

## Load rating/capacity

### Load rating (pull out strength)

1100 lbs

### Load rating (slip strength)

800 lbs

## Material/finish

### Finish

Electro-plated

### Material

Steel

## Resources

### Catalogs

[B-Line Safety Gratings Full Catalog](#)

[B-Line Series Strut Systems Catalog](#)

[Channel Nuts and Hardware Catalog Section](#)

### Specifications and datasheets

[Eaton Specification Sheet - N228ZN](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton N228ZN

Catalog Number: N228ZN

Eaton B-Line series spring nut, 0.85"Hx1.875"Lx1.375"W, Steel, Electro-plated, 3/8"-16 bolt size, 1100 lbs load, 800 lbs load



## General specifications

|                                |                      |
|--------------------------------|----------------------|
| Product Name                   | Catalog Number       |
| Eaton B-Line series spring nut | N228ZN               |
| UPC                            | Product Length/Depth |
| 781011403638                   | 1.875 in             |
| Product Height                 | Product Width        |
| 0.85 in                        | 1.375 in             |
| Product Weight                 | Certifications       |
| 0.083 lb                       | Not Applicable       |

## Model

### Bolt/thread/rod size

3/8"-16

### Product Category

Channel nuts

### Type

Nut without spring

## Load rating/capacity

### Load rating (pull out strength)

1100 lbs

### Load rating (slip strength)

800 lbs

## Material/finish

### Finish

Electro-plated

### Material

Steel

## Resources

### Catalogs

[B-Line Safety Gratings Full Catalog](#)

[B-Line Series Strut Systems Catalog](#)

[Channel Nuts and Hardware Catalog Section](#)

### Specifications and datasheets

[Eaton Specification Sheet - N228ZN](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)