

NEW
1" Trade Size

Non-Metallic Screw-on Connectors

Straight & 90° for Non-metallic, Liquid-tight Conduit, Type B



Unscrew the connector a full turn and still have a Listed liquid-tight installation!



NEW!
1" trade sizes

Straight Black 1" NMSC100BL


Straight Gray 1" NMSC100

Connector Components 90° Black 1" NMSC90100BL

Arlington's one-piece non-metallic straight and 90° **screw-on** connectors are now available in 1" trade sizes.

Designed for use on non-metallic, liquid-tight conduit, Type B and flexible non-metallic tubing, installation is fast and easy. These connectors screw on to conduit *by hand*, with *no tools* required.

The job looks great too. The outer body on NMSC series connectors overlaps the conduit, hiding the ugly cut ends when it's screwed on.



When fully tightened the internal taper squeezes onto the conduit forming a reliable liquid-tight seal. Plus, you can unscrew the connector a full turn and still have a Listed liquid-tight installation.

- Ships fully assembled
- Made of UV rated plastic for long outdoor life
- Our most economical liquid-tight connectors are available in straight and 90°, gray or black



GRAY

STRAIGHT • SCREW-ON

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	KO Size	Unit Pkg	Std Pkg
NMSC38	21005	3/8	1/2	25	100
NMSC50	21000	1/2	1/2	25	100
NMSC75	21010	3/4	3/4	25	100
NEW! NMSC100	14950	1	1	5	25



BLACK

STRAIGHT • SCREW-ON

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	KO Size	Unit Pkg	Std Pkg
NMSC38BL	21008	3/8	1/2	25	100
NMSC50BL	21002	1/2	1/2	25	100
NMSC75BL	21011	3/4	3/4	25	100
NEW! NMSC100BL	22700	1	1	5	25

90° • SCREW-ON

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	KO Size	Unit Pkg	Std Pkg
NMSC9038	21003	3/8	1/2	25	100
NMSC9050	21007	1/2	1/2	25	100
NMSC9075	21009	3/4	3/4	25	100
NEW! NMSC90100	14951	1	1	5	25

90° • SCREW-ON

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	KO Size	Unit Pkg	Std Pkg
NMSC9038BL	33805	3/8	1/2	25	100
NMSC9050BL	33810	1/2	1/2	25	100
NMSC9075BL	33815	3/4	3/4	25	100
NEW! NMSC90100BL	22701	1	1	5	25



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

NEW
1" Trade Size

Non-Metallic Screw-on Connectors

Straight & 90° for Non-metallic, Liquid-tight Conduit, Type B



Unscrew the connector a full turn and still have a Listed liquid-tight installation!



NEW!
1" trade sizes

Straight Black 1" NMSC100BL


Straight Gray 1" NMSC100

Connector Components 90° Black 1" NMSC90100BL

Arlington's one-piece non-metallic straight and 90° **screw-on** connectors are now available in 1" trade sizes.

Designed for use on non-metallic, liquid-tight conduit, Type B and flexible non-metallic tubing, installation is fast and easy. These connectors screw on to conduit *by hand*, with *no tools* required.

The job looks great too. The outer body on NMSC series connectors overlaps the conduit, hiding the ugly cut ends when it's screwed on.



When fully tightened the internal taper squeezes onto the conduit forming a reliable liquid-tight seal. Plus, you can unscrew the connector a full turn and still have a Listed liquid-tight installation.

- Ships fully assembled
- Made of UV rated plastic for long outdoor life
- Our most economical liquid-tight connectors are available in straight and 90°, gray or black



GRAY

STRAIGHT • SCREW-ON

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	KO Size	Unit Pkg	Std Pkg
NMSC38	21005	3/8	1/2	25	100
NMSC50	21000	1/2	1/2	25	100
NMSC75	21010	3/4	3/4	25	100
NEW! NMSC100	14950	1	1	5	25

90° • SCREW-ON

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	KO Size	Unit Pkg	Std Pkg
NMSC9038	21003	3/8	1/2	25	100
NMSC9050	21007	1/2	1/2	25	100
NMSC9075	21009	3/4	3/4	25	100
NEW! NMSC90100	14951	1	1	5	25



BLACK

STRAIGHT • SCREW-ON

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	KO Size	Unit Pkg	Std Pkg
NMSC38BL	21008	3/8	1/2	25	100
NMSC50BL	21002	1/2	1/2	25	100
NMSC75BL	21011	3/4	3/4	25	100
NEW! NMSC100BL	22700	1	1	5	25

90° • SCREW-ON

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	KO Size	Unit Pkg	Std Pkg
NMSC9038BL	33805	3/8	1/2	25	100
NMSC9050BL	33810	1/2	1/2	25	100
NMSC9075BL	33815	3/4	3/4	25	100
NEW! NMSC90100BL	22701	1	1	5	25



Arlington
1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com