



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NFFLDC40T Trun 128W Led Flood 40K

Cooper Lighting Solutions

| | |
|------------------|--|
| Catalog Number | NFFLDC40T |
| Manufacturer | Cooper Lighting Solutions |
| Description | Led Flood Light, Die-Cast Aluminum, 120 to 277 V Ac;347 V Ac;480 V Ac, 128 W, 70, 16900 LM Brightness (Lumens), 4000 K, Powder Coat, 15-15/16 In Length, 8-11/16 In Width, 12-11/16 In Height, Tempered Glass Lens Material, Trunion Mount, +40 °C Operating Temperature, -40 °C Operating Temperature, 60000 H Average Life, 5 Yr Warranty, 20 LB |
| Weight per unit | 22.9 (lbs/each) |
| Product Category | Led Floodlights |

Features

| | |
|-----------------|-----------------|
| amperage rating | 0.466 (at 277V) |
| Ballast Type | N/A |
| battery | N/A |
| Fixture Type | FLOODLIGHT |
| Lamp Type | LED |
| lumens | 16,932 |
| media | Yes |
| Number of Lamps | 2 |
| Shape | Rectangular |

Dimensions and Weight

| | |
|------|---|
| Size | 18.0 IN Length 7.5 IN Width 9.5 IN Height |
|------|---|

Descriptions

| | |
|------------------------|---|
| Description | TRUN 128W LED FLOOD 40K |
| extra long description | CLS NFFLD-C40-T NFFLD,129W,4000K,UN |
| Special Features | Die-cast aluminum housing, driver compartment and driver door |

Manufacturer Information

| | |
|-------|----------------|
| Brand | LUMARK |
| GTIN | 00080083801183 |
| UPC | 080083801183 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING |
| Type | FLOODLIGHT |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 22.85 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting
standard

TRUNNION

UL/cUL Listed - Wet Location;RoHS Compliant