



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **P050NGYA STR Male L/T Conn, 1/2", NM, Gy** *Hubbell Wiring Devices*

Catalog Number	P050NGYA
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Liquidtight System, Polytuff® Straight Male Liquid Tight Connector, 1/2", Non-Metallic, Gray
Weight per unit	0.0220 (lbs/each)
Product Category	Liquid Tight Fittings

### **Features**

connection	Cap Nut
Material	Nylon
pallet quantity	6400

### **Material, Color, and Finish**

Color	Gray
Finish	Smooth

### **Dimensions and Weight**

Size	1/2 in
------	--------

### **Descriptions**

Description	STR MALE L/T CONN, 1/2", NM, GY
extra long description	HWDK P050NGYA STR MALE L/T CONN, 1/
Features	Liquidtight tubing is designed to house and permanently protect underground cable from moisture, grit, rodents and other environmental hazards that can damage the cable over time. The Kellems brands of liquidtight — PolyTuff® I conduit and PolyTuff® II tubing —feature non-metallic, PVC-based construction, avoiding the challenges of corrosion while providing high strength, superior flexibility and outstanding handleability. When compared to metals, they can be deployed in flexible directions, even accomoda
Long Description	Kellems Wire Management, Liquidtight System, PolyTuff® Straight Male Liquid Tight Connector, 1/2", Non-Metallic, Gray
Product Type	PolyTuff® Fittings
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585339139
Manufacturers Part Number	P050NGYA
UPC	783585339139



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Stainless Steel EMT Conduit
Type	PolyTuff® Non-Metallic Liquidtight Fittings

## Packaging

Carton	25
Weight Per each	0.022

## Uses, Certifications, and Standards

Application	Fittings are to be used with PolyTuff® I and PolyTuff® II
environmental conditions	Suitable for use in wet locations when a listed sealing ring is used between box and fitting
Mounting	Between Enclosure and Conduit
nema rating	12;13;4X
standard	CSA Certified;UL Listed:UL50 Type 4X, 12 and 13