

Specifications

Photo is representative

Eaton PB2M-4XS

Eaton B-Line series push button enclosures, 5.75" height, 3" length, 3.25" width, NEMA 4X, Screw cover, PBM4XS enclosure, Surface mounted, Small single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

General specifications

PRODUCT NAME	Eaton B-Line series push button enclosures
CATALOG NUMBER	PB2M-4XS
UPC	782051138146
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	5.75 in
PRODUCT WIDTH	3.25 in
PRODUCT WEIGHT	2.1 lb
COMPLIANCES	Not Applicable
CERTIFICATIONS	Not Applicable
PRODUCT TYPE	Push button enclosures



Powering Business Worldwide

Material/finish

MATERIAL 304 stainless steel

WALL THICKNESS 16 gauge

FINISH COLOR #4 brushed

COLOR Gray

Standards

NEMA RATING 4X

COUNTRY OF ORIGIN US

Model

STYLE Small single door

MODEL PBM4XS enclosure

COVER TYPE Screw

MOUNTING METHOD Surface

MOUNTING HOLE DETAILS External mounting feet

SPECIAL FEATURES Removable cover, recessed pull ring, s.s. screws

Resources

CATALOGS [Pushbutton-enclosure-operator.pdf](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - PB2M-4XS](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2026 Eaton. All Rights Reserved.

Specifications

Photo is representative

Eaton PB2M-4XS

Eaton B-Line series push button enclosures, 5.75" height, 3" length, 3.25" width, NEMA 4X, Screw cover, PBM4XS enclosure, Surface mounted, Small single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

General specifications

PRODUCT NAME	Eaton B-Line series push button enclosures
CATALOG NUMBER	PB2M-4XS
UPC	782051138146
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	5.75 in
PRODUCT WIDTH	3.25 in
PRODUCT WEIGHT	2.1 lb
COMPLIANCES	Not Applicable
CERTIFICATIONS	Not Applicable
PRODUCT TYPE	Push button enclosures



Powering Business Worldwide

Material/finish

MATERIAL	304 stainless steel
WALL THICKNESS	16 gauge
FINISH COLOR	#4 brushed
COLOR	Gray

Standards

NEMA RATING	4X
COUNTRY OF ORIGIN	US

Model

STYLE	Small single door
MODEL	PBM4XS enclosure
COVER TYPE	Screw
MOUNTING METHOD	Surface
MOUNTING HOLE DETAILS	External mounting feet
SPECIAL FEATURES	Removable cover, recessed pull ring, s.s. screws

Resources

CATALOGS	Pushbutton-enclosure-operator.pdf
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PB2M-4XS

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

