



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PL2508 250MCM-6AWG 8PRT Multi-Tap Conn

Nsi Industries

Catalog Number	PL2508
Manufacturer	Nsi Industries
Description	The Polaris PL250-8 Uninsulated Multi-Tap Connector Features 8 Ports Sized For 250 MCM - 6 Awg Wires. The Body Is Made From Aluminum Alloy and Plated For Corrosion Resistance. Each Pass-Through Port Features A Hex Screw Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Trays, Panel Boards, Ducts, Raceways or Troughs.
Weight per unit	0.4800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Number of Conductors	8
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	250 MCM-6 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Aluminum
Finish	Chromated
Housing Material	Aluminum

Dimensions and Weight

Size	L=6.990 - W=.880 - H=1.130
------	----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	250MCM-6AWG 8PRT MULTI-TAP CONN
extra long description	NSI PL250-8 POLARIS Unins Multi-Tap
Features	The Polaris PL250-8 8-Port Uninsulated Connector provides the simplest solution for forming a secure connection between up to eight conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 250 MCM - 6 AWG wires and rated for 2000V, this uninsulated connector installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is plated for corrosion resistance and features ergonomic rounded corners. All-i
Long Description	The Polaris PL250-8 Uninsulated Multi-Tap Connector features 8 ports sized for 250 MCM - 6 AWG wires. The body is made from aluminum alloy and plated for corrosion resistance. Each pass-through port features a hex screw used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable trays, panel boards, ducts, raceways or troughs.
Product Type	Polaris Unins Multi-Tap 250 8 Port
Special Features	(8) 250 MCM-6 AWG - Dual Rated

Manufacturer Information

Brand	NSi
GTIN	00662381903068
Manufacturers Part Number	PL250-8
UPC	662381903068

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Un-Insulated Multi Cable

Packaging

Carton	1
Weight Per each	0.48

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B