



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PLG300 3" Recessed Plug *Appleton/Oz Gedney*

Catalog Number	PLG300
Manufacturer	Appleton/Oz Gedney
Description	Unilets Recessed Head Close-Up Plug, Size: 3 In, Material: Malleable Iron, Finish: Zinc Electroplate, Connection: Tapered MNPT, Standard: UI 886 (1203), UI File Number E10444, Csa C22.2 No. 25 and 30, Csa 065181, UI Listed For Class I, GR
Weight per unit	2.2 (lbs/each)
Product Category	Bar Hangers & Outlet Box Accy.

Features

connection	Tapered MNPT
Material	Malleable Iron

Material, Color, and Finish

Finish	Zinc Electroplate
--------	-------------------

Dimensions and Weight

Size	3
------	---

Descriptions

Description	3" RECESSED PLUG
extra long description	APP PLG-300 PLUG 3 REC HEAD CLOSE-
Long Description	UNILETS Recessed Head Close-Up Plug, Size: 3 IN, Material: Malleable Iron, Finish: Zinc Electroplate, Connection: Tapered MNPT, Standard: UL 886 (1203), UL File Number E10444, CSA C22.2 No. 25 And 30, CSA 065181, UL Listed For Class I, Gr
Product Type	Plug 3 Rec Head Close-Up Iron
Special Features	Accurately tapped, tapered threads for tight, rigid joints and ground continuity;Explosionproof, dust-ignitionproof;Smooth, rounded integral bushing in each hub protects conductor insulation

Manufacturer Information

Brand	Appleton
GTIN	00781381652551
Manufacturers Part Number	PLG-300
UPC	781381652551

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Recessed Head Close-Up Plug



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Package	25
Weight Per each	2.16

Uses, Certifications, and Standards

Application	For Use With Threaded Rigid Metal Conduit and IMC
standard	And Class III;Class II, Groups E, F, G;UL 886 (1203), UL File Number E10444, CSA C22.2 No. 25 And 30, CSA 065181, UL Listed For Class I, Groups B, C, D