



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN1438RL #14 Nyl RG Term *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | PN1438RL |
| Manufacturer | Panduit Corporation |
| Description | Ring Terminal, 18 – 14 Awg, 3/8" Stud Size, Nylon Insulated, Standard Package. |
| Weight per unit | 0.0004 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|----------|
| connection | Standard |
| insulation | Nylon |
| Material | Copper |
| Voltage Rating | 600 |
| Wire Size | #14 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Blue |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|------|
| Size | 3/8" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | #14 NYL RG TERM |
| extra long description | PAN PN14-38R-L Pan-Term® PN14-38R-L |
| Long Description | Ring Terminal, 18 – 14 AWG, 3/8" stud size, nylon insulated, standard package. |
| Product Type | Pan-Term® PN14-38R-L Loose Piece Ring Terminal |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983800261 |
| Manufacturers Part Number | PN1438RL |
| UPC | 074983800261 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Ring Terminal |

Packaging

| | |
|-----------------|--------|
| Carton | 50 |
| Weight Per each | 0.0004 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Enclosure | Ring shape |
| Mounting standard | 7/32 |
| | UL Listed 587H E52164, CSA Certified LR31212, Military QPL AS7928 (MS25036-110) |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |