



### Mid-size decorator wallplates

#### Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang




2-Gang




3-Gang



4-Gang





5-Gang



6-Gang

#### Decorator wallplates

Gang	Material	Color suffix	Catalog no.		
1-Gang	Polycarbonate	A, B, BK, BL, GY, LA, RD, V, W	<input type="checkbox"/> PJ26__		
	Thermoset	A, B, LA, V, W	<input type="checkbox"/> 2051__		
	302/304 Stainless steel	—	<input type="checkbox"/> 93934		
2-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	<input type="checkbox"/> PJ262__		
	Thermoset	A, LA, V, W	<input type="checkbox"/> 2052__		
	302/304 Stainless steel	—	<input type="checkbox"/> 93935		
3-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ263__		
	Thermoset	A, LA, V, W	<input type="checkbox"/> 2063__		
	302/304 Stainless steel	—	<input type="checkbox"/> 93936		
4-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ264__		
	Thermoset	A, LA, V, W	<input type="checkbox"/> 2064__		
5-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ265__		
6-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ266__		

#### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), BL (Blue), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



**Certification information:** 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**


 Indicates NAFTA compliant - Page Q-32

 RoHS compliant - Page Q-32


### Mid-size decorator wallplates

#### Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang




2-Gang




3-Gang



4-Gang





5-Gang



6-Gang

#### Decorator wallplates

Gang	Material	Color suffix	Catalog no.	 
1-Gang	Polycarbonate	A, B, BK, BL, GY, LA, RD, V, W	<input type="checkbox"/> PJ26__	•
	Thermoset	A, B, LA, V, W	<input type="checkbox"/> 2051__	• •
	302/304 Stainless steel	—	<input type="checkbox"/> 93934	• •
2-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	<input type="checkbox"/> PJ262__	•
	Thermoset	A, LA, V, W	<input type="checkbox"/> 2052__	• •
	302/304 Stainless steel	—	<input type="checkbox"/> 93935	• •
3-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ263__	•
	Thermoset	A, LA, V, W	<input type="checkbox"/> 2063__	• •
	302/304 Stainless steel	—	<input type="checkbox"/> 93936	• •
4-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ264__	•
	Thermoset	A, LA, V, W	<input type="checkbox"/> 2064__	• •
5-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ265__	•
6-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ266__	•

#### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), BL (Blue), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



**Certification information:** 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**

 Indicates NAFTA compliant - Page Q-32

 RoHS compliant - Page Q-32