

Specifications

Photo is representative

Eaton PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V, Three-phase, 4W, 600A, 42 circuit, Copper bus

General specifications

| | |
|-----------------------------|------------------------------------|
| PRODUCT NAME | Eaton Pow-R-Stock PRL2A panelboard |
| CATALOG NUMBER | PRL2A3600X42CL |
| UPC | 786687011125 |
| PRODUCT LENGTH/DEPTH | 85 in |
| PRODUCT HEIGHT | 7 in |
| PRODUCT WIDTH | 18 in |
| PRODUCT WEIGHT | 75 lb |
| COMPLIANCES | NEMA Compliant |
| CERTIFICATIONS | UL 67 |

Product specifications

| | |
|-------------------------------|------------------|
| TYPE | PRL2A Panelboard |
| AMPERAGE RATING | 600A |
| BUS MATERIAL | Copper |
| BUS RATING | 600 |
| FEED TYPE | Top |
| NUMBER OF CIRCUITS | 42 |
| NUMBER OF POLES | Single pole |
| OPERATING TEMPERATURE | 40°C |
| PHASE | Three phase |
| SHORT-CIRCUIT RATING | 35 A |
| WIRE SIZE | #4 A 350 |
| CIRCUIT BREAKER RATING | NEMA |
| CURRENT - MAX | 600 |
| NEMA RATING | NEMA |
| SERIES | PRL2A |
| VOLTAGE - MAX | 480 |



Powering Business Worldwide

Specifications

Photo is representative

Eaton PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V, Three-phase, 4W, 600A, 42 circuit, Copper bus

General specifications

| | |
|-----------------------------|------------------------------------|
| PRODUCT NAME | Eaton Pow-R-Stock PRL2A panelboard |
| CATALOG NUMBER | PRL2A3600X42CL |
| UPC | 786687011125 |
| PRODUCT LENGTH/DEPTH | 85 in |
| PRODUCT HEIGHT | 7 in |
| PRODUCT WIDTH | 18 in |
| PRODUCT WEIGHT | 75 lb |
| COMPLIANCES | NEMA Compliant |
| CERTIFICATIONS | UL 67 |

Product specifications

| | |
|-------------------------------|------------------|
| TYPE | PRL2A Panelboard |
| AMPERAGE RATING | 600A |
| BUS MATERIAL | Copper |
| BUS RATING | 600 |
| FEED TYPE | Top |
| NUMBER OF CIRCUITS | 42 |
| NUMBER OF POLES | Single pole |
| OPERATING TEMPERATURE | 40°C |
| PHASE | Three phase |
| SHORT-CIRCUIT RATING | 35 A |
| WIRE SIZE | #4 A 350 |
| CIRCUIT BREAKER RATING | NEMA |
| CURRENT - MAX | 600 |
| NEMA RATING | NEMA |
| SERIES | PRL2A |
| VOLTAGE - MAX | 480 |



Powering Business Worldwide