

# Eaton PRL2A3600X42CL

Catalog Number: PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V,  
Three-phase, 4W, 600A, 42 circuit, Copper bus

## General specifications



Product Name	Catalog Number
Eaton Pow-R-Stock PRL2A panelboard	PRL2A3600X42CL
UPC	Product Length/Depth
786687011125	85 in
Product Height	Product Width
7 in	18 in
Product Weight	Compliances
75 lb	NEMA Compliant
Certifications	
UL 67	

## Product specifications

### Type

PRL2A Panelboard

### Amperage Rating

600A

### Bus material

Copper

### Bus Rating

600 A

### Feed type

Top/bottom

### Number of circuits

42

### Number Of Poles

Single-pole, three-pole

### Operating Temperature

40°C

### Phase

Three-phase

### Short-circuit rating

35 A

### Wire size

#4 AWG-350 kcmil

### Circuit breaker rating

NEMA

### Current - max

600 A

### NEMA rating

NEMA 1, NEMA 3R

### Series

PRL2a

### Voltage - max

480 V

## Resources

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - PRL2A3600X42CL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton PRL2A3600X42CL

Catalog Number: PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V, Three-phase, 4W, 600A, 42 circuit, Copper bus

## General specifications



Product Name	Catalog Number
Eaton Pow-R-Stock PRL2A panelboard	PRL2A3600X42CL
UPC	Product Length/Depth
786687011125	85 in
Product Height	Product Width
7 in	18 in
Product Weight	Compliances
75 lb	NEMA Compliant
Certifications	
UL 67	

## Product specifications

### Type

PRL2A Panelboard

### Amperage Rating

600A

### Bus material

Copper

### Bus Rating

600 A

### Feed type

Top/bottom

### Number of circuits

42

### Number Of Poles

Single-pole, three-pole

### Operating Temperature

40°C

### Phase

Three-phase

### Short-circuit rating

35 A

### Wire size

#4 AWG-350 kcmil

### Circuit breaker rating

NEMA

### Current - max

600 A

### NEMA rating

NEMA 1, NEMA 3R

### Series

PRL2a

### Voltage - max

480 V

## Resources

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - PRL2A3600X42CL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)