



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS20AC3L 20A 120/277VAC B+S Wire 3W Lock SW Gy

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | PS20AC3L |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 3-Way Switch, 3 Poles, 3 Ways, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Brown, Grounding Connection, Toggle Actuator, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.22 LB |
| Weight per unit | 0.2240 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-----------------|
| action | TP |
| amperage rating | 20 |
| Contact Rating | 120/277V, 20Amp |
| insulation | False |
| Poles | 3-way |
| Switch Type | Toggle |
| Voltage | 120.0 V |

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|---------------------------------------|
| Description | 20A 120/277VAC B+S WIRE 3W LOCK SW GY |
| extra long description | P&S PS20AC3L 20A 120/277VAC B+S WIR |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007195637 |
| Manufacturers Part Number | PS20AC3L |
| UPC | 785007195637 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Industrial switches |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.224 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting

WALL

standard

CULUS, FEDSPEC, UL20