



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV1090EL00 1IN PVC Coated Rigid 90

*Calpipe Industries, Inc*

|                  |   |
|------------------|---|
| Catalog Number   | PV1090EL00  |
| Manufacturer     | Calpipe Industries, Inc   |
| Description      | PVC Coated Steel Rigid Conduit Standard Radius Elbow, Standard Radius Type; Steel Material; 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior Finish; UI 6, CuI Approval; Ansi C80.1, Nema RN-1 Applicable Standard; 20 Standard Package |
| Weight per unit  | 2.1 (lbs/each)  |
| Product Category | Rigid Conduit Fittings - Steel  |

### Features

|                     |                       |
|---------------------|-----------------------|
| Applicable Standard | ANSI C80.1, NEMA RN-1 |
| Bend Angle          | 90 Degree             |
| Bend Radius         | 5.75 INCH             |
| End Type            | THREADED              |
| Material            | Steel                 |

### Material, Color, and Finish

|        |  |
|--------|--|
| Finish | 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior |
|--------|--|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Additional Information | Length 8 Inch; Constructional Feature Corrosion Resistant; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mills,  |
| Commodity Description  | Rigid Conduit Fittings - Steel  |
| Description            | 1IN PVC COATED RIGID 90   |
| extra long description | STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 1 INCH TRADE SIZE; THREADED END TYPE; 90 DEGREE BEND ANGLE; 5.75 INCH BEND RADIUS; LENGTH 8 INCH; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; APPLICATION PETROCHEMICAL, WATER AND WASTEWATER TREATMENT FACILITY, TRANSPORTATION AND INFRASTRUCTURE, FOOD, DAIRY AND BEVERAGE, MINING, MARINE AND COASTAL FACILITY, CHEMICAL PLANTS, STEEL MILL |
| Long Description       | PVC COATED STEEL RIGID CONDUIT STANDARD RADIUS ELBOW, STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 20 STANDARD PACKAGE   |
| Product Type           | PVC Coated Steel Rigid Conduit Standard Radius Elbow  |

## Manufacturer Information

|                           |                         |
|---------------------------|-------------------------|
| Brand                     | Calpipe Industries, Inc |
| GTIN                      | 00847656053895          |
| Manufacturers Part Number | PV1090EL00              |
| Model                     | PV                      |
| UPC                       | 847656053895            |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS |
| Type                 | STANDARD RADIUS                                 |

## Trade Size

|            |        |
|------------|--------|
| Trade Size | 1 INCH |
|------------|--------|

## Packaging

|                  |      |
|------------------|------|
| Carton           | 1    |
| Standard Package | 20   |
| Weight Per each  | 2.13 |

## Uses, Certifications, and Standards

|          |           |
|----------|-----------|
| Approval | UL 6, CUL |
|----------|-----------|