



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PS5266XHG Straight Blade Plug 3W 15A 125V HG

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | PS5266XHG   |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Hospital Grade Plug, 15 A, 125 V, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 1.516 In;0.230 to 0.690 In (Cord) Diameter, 2.791 In Length, #18 to #10 Awg Wire Size, Chemical Resistant, Impact Resistant, Corrosion Resistant, 0.164 LB |
| Weight per unit  | 0.1632 (lbs/each)   |
| Product Category | Plugs, Connectors, Inlets, Out  |

### Features

|                 |                |
|-----------------|----------------|
| amperage rating | 15             |
| connection      | Wire Grounding |
| Poles           | Double Pole    |
| Voltage         | 125.0 V        |
| Voltage Rating  | 125            |

### Dimensions and Weight

|      |        |
|------|--------|
| Size | 2.8 in |
|------|--------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | STR BLD PLUG 3W 15A 125V HG         |
| extra long description | P&S PS5266XHG STR BLD PLUG 3W 15A 1 |

### Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007236774   |
| Manufacturers Part Number | PS5266XHG        |
| UPC                       | 785007236774     |

### Taxonomies, Classifications, and Categories

|                      |                                    |
|----------------------|------------------------------------|
| Category Description | Industrial cord connectors         |
| Type                 | Hospital Grade Plug Straight Blade |

### Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 10     |
| Package         | 50     |
| Weight Per each | 0.1632 |

### Uses, Certifications, and Standards

|          |                        |
|----------|------------------------|
| standard | FEDSPEC, CULUS, UL 498 |
|----------|------------------------|