



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV44XS Encl 4H N4X SS4 VRT PB

*Cooper B-Line/Cable Tray*

Catalog Number	PV44XS
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Push Button Enclosures, 10.25" Height, 2.75" Length, 3.25" Width, Nema 4X, Screw Cover, PV4XS Enclosure, Surface Mounted, Medium Single Door, External Mounting Feet, 304 Stainless Steel, Oil-Resistant Gasket
Weight per unit	4.0 (lbs/each)
Product Category	Control Station Enclosures

### Features

dimensions	2.7500 IN X 3.2500 IN X 10.2500 IN
Material	304 Stainless Steel

### Material, Color, and Finish

Color	Gray
-------	------

### Descriptions

Description	ENCL 4H N4X SS4 VRT PB
extra long description	B-LINE PV4-4XS TYPE 12 STAINLESS VE
Features	Eaton's B-Line series push button enclosures provide reliable environmental protection and are designed to mount standard 30.5 mm or miniature 22.5 mm oil-tight pushbuttons, pilot lights and switches
Long Description	Eaton B-Line series push button enclosures, 10.25" height, 2.75" length, 3.25" width, NEMA 4X, Screw cover, PV4XS enclosure, Surface mounted, Medium single door, External mounting feet, 304 stainless steel, Oil-resistant gasket
Product Type	Type 12 Stainless Vert Pushbutton Enc
Special Features	Removable cover, recessed pull ring, s.s. screws

### Manufacturer Information

Brand	Eaton
GTIN	00782051137002
Manufacturers Part Number	PV4-4XS
UPC	782051137002

### Taxonomies, Classifications, and Categories

Category Description	STANDARD DUTY PUSHBUTTONS (10250H-)
Type	Push button enclosures

### Packaging

Carton	1
Weight Per each	4.019



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
nema rating	4X
standard	Not Applicable, Not Applicable