

Specifications



Eaton QBCAF1020

Eaton QB AFCI circuit breaker, Type QBCAF 1-inch Circuit Interrupter, Single-pole, 120/240V, 10 kAIC, Combination AFCI, 20A

General specifications

PRODUCT NAME	Eaton QB AFCI circuit breaker
CATALOG NUMBER	QBCAF1020
UPC	786685244914
PRODUCT LENGTH/DEPTH	5.1 in
PRODUCT HEIGHT	1.2 in
PRODUCT WIDTH	3.3 in
PRODUCT WEIGHT	0.2 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated, for use in Sumter panels

Physical Attributes

NUMBER OF POLES	Single-pole
TYPE	AFCI circuit breakers

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	10 kAIC

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBCAF1020
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications



Eaton QBCAF1020

Eaton QB AFCI circuit breaker, Type QBCAF 1-inch Circuit Interrupter, Single-pole, 120/240V, 10 kAIC, Combination AFCI, 20A

General specifications

PRODUCT NAME	Eaton QB AFCI circuit breaker
CATALOG NUMBER	QBCAF1020
UPC	786685244914
PRODUCT LENGTH/DEPTH	5.1 in
PRODUCT HEIGHT	1.2 in
PRODUCT WIDTH	3.3 in
PRODUCT WEIGHT	0.2 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated, for use in Sumter panels

Physical Attributes

NUMBER OF POLES	Single-pole
TYPE	AFCI circuit breakers

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	10 kAIC

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBCAF1020
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.