



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## QBGFEP1040 Bolt On GFCB W/PCB 10KAIC 30A 30MA Trip

*Eaton Corp*

Catalog Number	QBGFEP1040
Manufacturer	Eaton Corp
Description	Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Breaker, Single-Pole, 30 Ma Trip Sensitivity, 40A, 10 Kaic, 120V, Bolt-On Mounting
Weight per unit	1.4 (lbs/each)
Product Category	On Circuit Breakers

### Features

dimensions	6.0000 IN X 3.5000 IN X 1.0000 IN
interrupt rating	10
Poles	1
Voltage Rating	120 V

### Descriptions

Description	BOLT ON GFCB W/PCB 10KAIC 30A 30MA TRIP
extra long description	ETN QBGFEP1040 BOLT ON GFCB W/PCB 1
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Breaker, Single-pole, 30 mA Trip Sensitivity, 40A, 10 kAIC, 120V, Bolt-on mounting
Product Type	Bolt On GFCB W/PCB 10KAIC 30A 30MA Trip
Special Features	30 mA Trip Sensitivity

### Manufacturer Information

Brand	Eaton
GTIN	00786679117293
Manufacturers Part Number	QBGFEP1040
UPC	786679117293

### Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

### Packaging

Carton	1
Weight Per each	1.4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy  
Marine Vessels and Equipment - Marine Vessels and Equipment -  
Other Datacenters - IT Space: CI and Hyper  
Converged Other Generation - Conventional Energy - Conventional  
Energy

standard

UL 943