

# Specifications

## Eaton QBGFEP2040



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 40A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, QBGF

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2040
UPC	786679145180
PRODUCT LENGTH/DEPTH	6.125 in
PRODUCT HEIGHT	2.25 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.85 lb
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



### Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

### Performance Ratings

AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Miscellaneous	
SPECIAL FEATURES	Bolt-on mounting

Resources	
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBGFEP2040</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.      Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton QBGFEP2040

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,Bolt-on mounting,40A,10 kAIC,Two-pole,120/240V,Non-Interchangeable,QBGF



### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2040
UPC	786679145180
PRODUCT LENGTH/DEPTH	6.125 in
PRODUCT HEIGHT	2.25 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.85 lb
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



### Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

### Performance Ratings

AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

## Miscellaneous

### SPECIAL FEATURES

Bolt-on mounting

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - QBGFEP2040](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



#### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

