

# Specifications



Photo is representative



## Eaton R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

### General specifications

<b>PRODUCT NAME</b>	Eaton rotary disconnect switch
<b>CATALOG NUMBER</b>	R5A3040U
<b>UPC</b>	786685402888
<b>PRODUCT LENGTH/DEPTH</b>	2.57 in
<b>PRODUCT HEIGHT</b>	3.35 in
<b>PRODUCT WIDTH</b>	1.77 in
<b>PRODUCT WEIGHT</b>	0.5 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	CCC Marked
<b>CERTIFICATIONS</b>	CSA Certified EN Listed IEC Rated UL 508
<b>CATALOG NOTES</b>	Suitable as motor disconnect



Powering Business Worldwide

## Physical Attributes

**NUMBER OF POLES** Three-pole

**SERIES** R5

## Miscellaneous

**PRODUCT CATEGORY** Rotary Switch

## Performance Ratings

**AMPERAGE RATING** 40A

**VOLTAGE RATING** 600 V

## Resources

**CATALOGS** [Commercial Distribution, Switching Devices, Volume 2, Tab 1](#)

**MULTIMEDIA** [Switching Devices Flex Center](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - R5A3040U](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

### General specifications

<b>PRODUCT NAME</b>	Eaton rotary disconnect switch
<b>CATALOG NUMBER</b>	R5A3040U
<b>UPC</b>	786685402888
<b>PRODUCT LENGTH/DEPTH</b>	2.57 in
<b>PRODUCT HEIGHT</b>	3.35 in
<b>PRODUCT WIDTH</b>	1.77 in
<b>PRODUCT WEIGHT</b>	0.5 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	CCC Marked
<b>CERTIFICATIONS</b>	CSA Certified EN Listed IEC Rated UL 508
<b>CATALOG NOTES</b>	Suitable as motor disconnect



Powering Business Worldwide

## Physical Attributes

**NUMBER OF POLES** Three-pole

**SERIES** R5

## Miscellaneous

**PRODUCT CATEGORY** Rotary Switch

## Performance Ratings

**AMPERAGE RATING** 40A

**VOLTAGE RATING** 600 V

## Resources

**CATALOGS** [Commercial Distribution, Switching Devices, Volume 2, Tab 1](#)

**MULTIMEDIA** [Switching Devices Flex Center](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - R5A3040U](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

