

Eaton RDCH42B200I

Catalog Number: RDCH42B200I

Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit, Main circuit breaker, 200 A, Retro size group d, Cover height: 47 in, Cover width: 24 in, NEMA 1, 25 kAIC, CH, Surface, flush, 42 Circuits, Single-phase, 0.75 in, #1 AWG-300 kcmil

General specifications



Product Name

Eaton CH retrofit kit

UPC

786685211114

Product Height

45 in

Product Weight

1 lb

Certifications

UL 67

Catalog Number

RDCH42B200I

Product Length/Depth

6 in

Product Width

22 in

Warranty

1 year

Catalog Notes

Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.

Product specifications

Type

Retrofit kit

Amperage Rating

200 A

Main circuit breaker

CH

Mounting

Surface, flush

Number of circuits

42

Phase

Single-phase

Wire size

#1 AWG-300 kcmil

Box size

Retro size group d

Cover height

47

Cover width

24

Enclosure

NEMA 1

Interrupt rating

25 kAIC

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - RDCH42B200I](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)

Eaton RDCH42B200I

Catalog Number: RDCH42B200I

Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit, Main circuit breaker, 200 A, Retro size group d, Cover height: 47 in, Cover width: 24 in, NEMA 1, 25 kAIC, CH, Surface, flush, 42 Circuits, Single-phase, 0.75 in, #1 AWG-300 kcmil

General specifications



Product Name

Eaton CH retrofit kit

UPC

786685211114

Product Height

45 in

Product Weight

1 lb

Certifications

UL 67

Catalog Number

RDCH42B200I

Product Length/Depth

6 in

Product Width

22 in

Warranty

1 year

Catalog Notes

Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.

Product specifications

Type

Retrofit kit

Amperage Rating

200 A

Main circuit breaker

CH

Mounting

Surface, flush

Number of circuits

42

Phase

Single-phase

Wire size

#1 AWG-300 kcmil

Box size

Retro size group d

Cover height

47

Cover width

24

Enclosure

NEMA 1

Interrupt rating

25 kAIC

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - RDCH42B200I](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)