

Eaton RES-60

Catalog Number: RES-60

Eaton Bussmann series RES fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Standard, 10, 600 V

General specifications



| | |
|--------------------------------|-----------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series RES fuse | RES-60 |
| UPC | EAN |
| 051712110600 | 5027590465991 |
| Product Length/Depth | Product Height |
| 0.78 in | 5.5 in |
| Product Width | Product Weight |
| 0.78 in | 0.29 lb |
| Warranty | Compliances |
| Not Applicable | Not Applicable |

Electrical rating

Amperage Rating

60 A

Interrupt rating

10 kAIC at 250 Vac

Voltage rating

600 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[Edison full line catalog 1005](#)

[Bussmann series complete full line catalog no. 1007](#)

[RES-60~SUPER LAG RENEWABLE FUSE 60/600](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - RES-60](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton RES-60

Catalog Number: RES-60

Eaton Bussmann series RES fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Standard, 10, 600 V

General specifications



| | |
|--------------------------------|-----------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series RES fuse | RES-60 |
| UPC | EAN |
| 051712110600 | 5027590465991 |
| Product Length/Depth | Product Height |
| 0.78 in | 5.5 in |
| Product Width | Product Weight |
| 0.78 in | 0.29 lb |
| Warranty | Compliances |
| Not Applicable | Not Applicable |

Electrical rating

Amperage Rating

60 A

Interrupt rating

10 kAIC at 250 Vac

Voltage rating

600 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[Edison full line catalog 1005](#)

[Bussmann series complete full line catalog no. 1007](#)

[RES-60~SUPER LAG RENEWABLE FUSE 60/600](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - RES-60](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)