



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RDCH42B200I CH Retrofit Kit Int Only 1 PH 200A Main BKR 42 CKT

*Eaton Corp*

Catalog Number	RDCH42B200I
Manufacturer	Eaton Corp
Description	Eaton CH 3/4-Inch Loadcenter Retrofit Stocking Kit, Main Circuit Breaker, 200 A, Retro Size Group D, Cover Height: 47 In, Cover Width: 24 In, Nema 1, 25 Kaic, CH, Surface, Flush, 42 Circuits, Single-Phase, 0.75 In, #1 Awg-300 Kcmil
Weight per unit	22.0 (lbs/each)
Product Category	Load Center Accessories

### Features

dimensions	6.0000 IN X 22.0000 IN X 45.0000 IN
------------	-------------------------------------

### Descriptions

Description	CH RETROFIT KIT INT ONLY 1 PH 200A MAIN BKR 42 CKT
extra long description	ETN RDCH42B200I Eaton CH retrofit k
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit,Main circuit breaker,200 A,Retro size group d,Cover height: 47 in,Cover width: 24 in,NEMA 1,25 kAIC,CH,Surface, flush,42 Circuits,Single-phase,0.75 in,#1 AWG-300 kcmil
Product Type	Eaton CH Retrofit Kit

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685211114
Manufacturers Part Number	RDCH42B200I
UPC	786685211114

### Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Accessory

### Packaging

Carton	1
Weight Per each	22



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Other
standard	UL 67