



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RE1308 1/2X3/8 Reducing Bushing

*Crouse-Hinds*

Catalog Number	RE1308
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Re Reducer, Rigid/Imc, End 1: 1/2" NPT, End 2: 3/8" NPT, Steel
Weight per unit	0.0300 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Threaded
dimensions	0.8400 IN X 0.6300 IN X 0.8400 IN
Material	FERALOY IRON ALLOY

### Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

### Dimensions and Weight

Size	1/2 To 3/8 In
------	---------------

### Descriptions

Description	1/2X3/8 REDUCING BUSHING
extra long description	CRS-H RE1308 1/2 TO 3/8 REDUCING BU
Features	Crouse-Hinds series RE, REA and REC explosionproof reducers are used in rigid/IMC conduit systems to reduce conduit hubs to a smaller size (RE), connect two different sizes of conduit together (REC), or enlarge drilled and tapped openings by one NPT size (REA). PLG explosionproof plugs are used for closing threaded conduit hubs.
Long Description	Eaton Crouse-Hinds series RE reducer, Rigid/IMC, End 1: 1/2" NPT, End 2: 3/8" NPT, Steel
Product Type	1/2 to 3/8 Reducing Bush
Special Features	Reducing fitting

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274592541
Manufacturers Part Number	RE1308
UPC	782274592541

### Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	REDUCER



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	100
Weight Per each	0.03

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group A B C D, Class II Div 1 Group E F G, Class II
	Div 2 Group F G, Class III
standard	UL 886, CSA C22.2