



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RF9540NDLA Dim Aspirerf Deco MSTR All-Load Neut La *Eaton Wiring Devices*

Catalog Number	RF9540NDLA
Manufacturer	Eaton Wiring Devices
Description	Eaton Z-Wave Dimmer Switch, Light Almond, Single Pole, 120 Vac, 300W Dimmable Led/CFL, 600W Incandescent, Halogen, Magnetic Low Voltage, Electronic Low Voltage, Dimmer Switch, Multi-Location, 32°F to 104°F (0°C to 40°C) 739033
Weight per unit	0.3700 (lbs/each)
Product Category	Lighting Dimmers

Features

dimensions	1.3600 IN X 1.5000 IN X 3.8100 IN
media	Yes
Voltage Rating	120 V
Wattage	300 W (LED, CFL), 600 W (INC/HAL, ELV, MLV)

Descriptions

Description	DIM ASPIRERF DECO MSTR ALL-LOAD NEUT LA
extra long description	EWD RF9540-NDLA Dim Aspirerf Deco M
Features	Add wireless control to your lighting with Eaton's Z-Wave wireless collection to make your home connected and smart. This complete offering of lighting controls is easy to install, requires no special wiring and is perfect for both existing homes and new construction. With Z-Wave based technology you can create your own wireless home network to enhance security, control appliances, set the right mood and save energy. Select from a range of styles and colors to match your home's decor.
Long Description	Eaton Z-Wave dimmer switch, Light Almond, Single pole, 120 Vac, 300W Dimmable LED/CFL, 600W Incandescent, Halogen, Magnetic Low Voltage, Electronic Low Voltage, Dimmer switch, Multi-location, 32°F to 104°F (0°C to 40°C) 739033
Product Type	Dim Aspirerf Deco MSTR All-Load Neut La
Special Features	RF Controls Dimmers

Manufacturer Information

Brand	Eaton
GTIN	00032664739033
Manufacturers Part Number	RF9540-NDLA
UPC	032664739033

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Package 6

Weight Per each 0.37

Uses, Certifications, and Standards

Application Residential Bldgs & Facilities - Residential Bldgs & Facilities -
Other

Operating Temperature 32 to 104 °F (0 to 40 °C)

standard NOM,cULus Listed