



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **RHCL453PTC Radiant CFL/Led SP/3W 450W Tri-Color** *Pass & Seymour/Legrand*

Catalog Number	RHCL453PTC
Manufacturer	Pass & Seymour/Legrand
Description	450W 120V Radiant CFL/Fed Single Pole/3-Way Dimmer, Tri-Color
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers

### **Features**

Connection Type	Screw Terminal
load	LED, Incandescent, CFL
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
Switch Type	Paddle
Voltage	120.0 V
Voltage Rating	120
Wattage	700

### **Material, Color, and Finish**

Color	Ivory, Light Almond, White
-------	----------------------------

### **Descriptions**

Description	RADIANT CFL/LED SP/3W 450W TRI-COLOR
extra long description	P&S RHCL453PTC RADIANT CFL/LED SP/3
Long Description	450W 120V Radiant CFL/FED Single Pole/3-Way Dimmer, Tri-Color
Product Type	Radiant CFL/Led SP/3W 450W, Tri-Color
Special Features	The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes. This dimmer is multi-location dimming with 3-Way wiring for simple installation.

### **Manufacturer Information**

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007053487
Manufacturers Part Number	RHCL453PTC
UPC	785007053487

### **Taxonomies, Classifications, and Categories**

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 15.0

## Packaging

Carton ..... 1

Package ..... 24

Weight Per each ..... 0.25

## Uses, Certifications, and Standards

Application ..... Residential

Enclosure ..... Thermoplastic

environmental conditions ..... Humidity: Less than 95% non condensing

Mounting ..... Box Mount

standard ..... CULUS, UL, CSA Listed, cULus, UL Listed