

# Eaton RSPF2403SA2A

Catalog Number: RSPF2403SA2A

Eaton Surge Protection Device for sub-panel, RSPF Series, F Frame, 120/208Y, 127/220Y, 240D rating, integrated, Basic feature package plus filtering, Direct Bus Mounted



## General specifications

Product Name	Catalog Number
Eaton RSPF surge protection device	RSPF2403SA2A
UPC	Product Length/Depth
786689030605	5 in
Product Height	Product Width
7.5 in	5 in
Product Weight	Warranty
2.38 lb	2 year
Certifications	
UL 1449	
UL Listed	

## Product specifications

### Type

SPD

### Special features

Meets or exceeds the requirements specified in IBC ©2006, CBC2007, and UBC@Zone 4

### Accessories

Basic Plus Filtering

### Frequency rating

50/60 Hz

### Nominal Discharge Current

20 kA

### Used with

Direct bus mounted

### Phase

Three-phase

### Operating temperature

-40 to 60 °C

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - RSPF2403SA2A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton RSPF2403SA2A

Catalog Number: RSPF2403SA2A

Eaton Surge Protection Device for sub-panel, RSPF Series, F Frame, 120/208Y, 127/220Y, 240D rating, integrated, Basic feature package plus filtering, Direct Bus Mounted



## General specifications

Product Name	Catalog Number
Eaton RSPF surge protection device	RSPF2403SA2A
UPC	Product Length/Depth
786689030605	5 in
Product Height	Product Width
7.5 in	5 in
Product Weight	Warranty
2.38 lb	2 year
Certifications	
UL 1449	
UL Listed	

## Product specifications

### Type

SPD

### Special features

Meets or exceeds the requirements specified in IBC ©2006, CBC2007, and UBC@Zone 4

### Accessories

Basic Plus Filtering

### Frequency rating

50/60 Hz

### Nominal Discharge Current

20 kA

### Used with

Direct bus mounted

### Phase

Three-phase

### Operating temperature

-40 to 60 °C

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - RSPF2403SA2A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)