

# Specifications

Photo is representative



## Eaton S10N06P76P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 58AP, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.75 KVA, indoor-outdoor, 3C

### Physical Attributes

<b>COIL MATERIAL</b>	Aluminum
<b>DESIGN</b>	EP
<b>ENCLOSURE</b>	NEMA 3R
<b>FRAME</b>	58AP
<b>TAP SIZE</b>	None
<b>TYPE</b>	General-Purpose Encapsulated Transformer
<b>WIRING CONNECTION</b>	3C

### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose encapsulated transformer
<b>CATALOG NUMBER</b>	S10N06P76P
<b>UPC</b>	786680073663
<b>PRODUCT LENGTH/DEPTH</b>	5.99 in
<b>PRODUCT HEIGHT</b>	11.68 in
<b>PRODUCT WIDTH</b>	4.99 in
<b>PRODUCT WEIGHT</b>	21 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

# Specifications

Photo is representative



## Eaton S10N06P76P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 58AP, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.75 KVA, indoor-outdoor, 3C

### Physical Attributes

<b>COIL MATERIAL</b>	Aluminum
<b>DESIGN</b>	EP
<b>ENCLOSURE</b>	NEMA 3R
<b>FRAME</b>	58AP
<b>TAP SIZE</b>	None
<b>TYPE</b>	General-Purpose Encapsulated Transformer
<b>WIRING CONNECTION</b>	3C

### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose encapsulated transformer
<b>CATALOG NUMBER</b>	S10N06P76P
<b>UPC</b>	786680073663
<b>PRODUCT LENGTH/DEPTH</b>	5.99 in
<b>PRODUCT HEIGHT</b>	11.68 in
<b>PRODUCT WIDTH</b>	4.99 in
<b>PRODUCT WEIGHT</b>	21 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed