



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S11252 Wi-Fi 9.5W Led A19 RGB/Tunable Bulb

Satco

Catalog Number	S11252
Manufacturer	Satco
Description	9.5 Watt - A19 Led Lamp - RGB and Tunable White - Starfish lot - 120 Volts - 800 Lumens
Weight per unit	0.2300 (lbs/each)
Product Category	Lighting

Features

average life	25000
Base	E26
beam angle	220
dimmable	Yes-Dimmable
lumens	800
Material	Plastic; Aluminum
Power Factor	0.6
Shape	A19
Voltage Rating	120
Warranty	3 Year Limited - 3 hr per day
Wattage	9.5

Material, Color, and Finish

color rendering index (cri)	80+
color temperature	2700 to 5000
Finish	white

Dimensions and Weight

Size	4.57
------	------

Descriptions

Description	WI-FI 9.5W LED A19 RGB/TUNABLE BULB
extra long description	SATCO S11252 9.5A19/LED/RGB/TW/SF
Long Description	9.5 Watt - A19 LED Lamp - RGB and Tunable White - Starfish IOT - 120 Volts - 800 Lumens
Product Type	9.5A19/Led/RGB/TW/SF
Special Features	Warranty: 5-Years ; Location Rating: Damp ; Operating Temp: -20C (-4F) to +45C (+113F) ; Dimmable Text: Only with Starfish App ; Material: Aluminum / Plastic ; Indoor Outdoor: Indoor ; Color Temp: Warm to Cool White ; Efficacy: 84.21 LPW ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor ; Lamp Filament: LED ; ANSI Base: E26 ; Amps: 0.079A ; T24 Compliant: False



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923112522
Manufacturers Part Number	S11252
UPC	045923112522

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	LED General Service

Packaging

Carton	1
Weight	0.15
Weight Per each	0.23

Uses, Certifications, and Standards

Application	LED
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus - Certified;cULus - Listed