



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S11852 8" 22W Led Commercial DNLTL 27K/3K/35K/4K/5K 2200L

Satco

Catalog Number	S11852
Manufacturer	Satco
Description	22-Watt Commercial Led Downlight - 8 In. - CCT Adjustable - 120-277 Volts - Econo
Weight per unit	1.8 (lbs/each)
Product Category	Lighting

### Features

average life	50000
Base	Integrated LED
beam angle	90

### Material, Color, and Finish

Finish	white
--------	-------

### Dimensions and Weight

Size	H:3.94 D:9.93
------	---------------

### Descriptions

Description	8" 22W LED COMMERCIAL DNLTL 27K/3K/35K/4K/5K 2200L
extra long description	SATCO S11852 22WLED/CDL/8/CCT/120-2
Long Description	22-Watt Commercial LED Downlight - 8 in. - CCT Adjustable - 120-277 Volts - Econo
Product Type	22WLED/CDL/8/CCT/120-277
Special Features	Lawful for sale in California ; Lumens: 2200 ; CCT: 2700K/3000K/3500K/4000K/5000K ; Color Temperature: Warm to Cool White ; Dimmable: Yes-Dimmable ; Dimmable Text: 0-10V Dimming Only ; Includes: 18-inch whip ; DLC Approved: No ; Energy Star: Yes ; Warranty: 5 Year Limited - Fixtures ; ADA Compliant: Yes ; Air Tight: Yes ; IC Rated: Yes ; Amps: 0.190A ; CCT Selectable: Yes ; FCC Compliant: Yes ; CFL Equivalent: 32W ; Indoor/Outdoor: Indoor and Outdoor ; Lens Finish: Plastic ; Lens Material: Polycarbonate (P)

### Manufacturer Information

Brand	Satco
GTIN	00045923118524
Manufacturers Part Number	S11852
UPC	045923118524



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RECESSED

## Packaging

Carton	1
Package	4
Weight Per each	1.83

## Uses, Certifications, and Standards

standard	cETLus - Listed
----------	-----------------